2680 World Wide Voltage Series



FEATURES

- > World wide voltage/frequency operation
- > Oil-less operation
- > Stainless steel valving components
- > Epoxy coated wetted parts
- > Aluminum die-cast components
- > Proven WOB-L technology
- > High performance tapered piston seals
- > Thermally protected motor
- > Lightweight, impact resistant fan guards
- > Internal 9 blade cooling air flow fans
- > Designed and tested per Agency standards
- > RoHS & REACH compliant
- > Field serviceable

Declaration documentation available upon request

TYPICAL APPLICATIONS

- > Blood & Laboratory Analyzers
- > Respirators/Respiratory Therapy
- > Medical/Dental/Optical Equipment
- > Industrial/Manufacturing Equipment
- > Business Equipment/Food & Beverage Equipment



2680CWW40 (100-127/50/60/1 & 200-240/50/60/1)






2680 World Wide Voltage Series

Flow	4.5 cfm (127 l/min)
Max. pressure	100 psi (6.9 bar)
Max. vacuum	92% local barometer







NOTE: All test values are nominal and for reference only. They are not guaranteed maximum or minimum limits, nor do they imply mean or median.


PERFORMANCE DATA		T17	r-0418		
Model Number		2680CWW40			
Head configuration		Pressure or vacuum parallel flow			
Stroke	0.40 in. (10.16 mm)				
Nominal voltage input range	100 - 127V 50Hz	100 - 127V 60Hz	200 - 240V 50Hz	200 - 240V 60Hz	
Max. open air flow	3.6 cfm (102 l/min)	4.5 cfm (127 l/min)	3.6 cfm (102 l/min)	4.5 cfm (127 l/min)	
Max. rated pressure	100 psi (6.9 bar)	100 psi (6.9 bar)	100 psi (6.9 bar)	100 psi (6.9 bar)	
Current at rated pressure	5.0A - 4.9A	6.2A - 5.2A	2.6A - 2.4A	3.3A - 2.9A	
Power at rated pressure	490W - 560W	615W - 650W	507W - 543W	646W - 679W	
Speed at rated pressure	1395 rpm - 1440 rpm	1647 rpm - 1725 rpm	1394 rpm - 1432 rpm	1634 rpm - 1707 rpm	
Maximum rated vacuum	92% local barometer	92% local barometer	92% local barometer	92% local barometer	
Maximum pressure restart	Consult factory				
Maximum vacuum restart	Consult factory				

ELECTRICAL DATA				
Motor type (Capacitance)	P.S.C. [35 μF]			
Motor locked rotor current	17.0 - 21.2A	15.2 - 20.4A	8.4 - 10.1A	7.8 - 9.5A
Motor insulation class	В			
Thermal switch (Open temperature)	Yes [266°F (130°C)]			
Lead wire color, gauge	Lead wire connection dependant on voltage requirement, consult wiring diagram below, 18 AWG			
Capacitor lead wire color, gauge	Brown, brown 18 AWG			

GENERAL DATA		
Operating ambient temperature	50° to 104°F (10°C TO 40°C)*	
Safety Certification	Declaration of Incorporation documentation available upon request	
Net weight	20.9 lbs (9.5 kg)	

*Broader ambient operating ranges may be possible depending on your specific application. Please consult factory regarding your particular system needs.

PRODUCT DIMENSIONS



PUMP AND COMPRESSOR SOLUTIONS FOR OEMS WORLDWIDE





T +86 510 6878 2258

F +49 8141 8892136 F +86 510 6878 2200 F +1 920 4514276 thomas.de@gardnerdenver.com thomas.cn@gardnerdenver.com td.usa@gardnerdenver.com

by Gardner Denver

T +1 920 4574891

The information presented in this material is based on technical data and test results of nominal units. It is believed to be accurate and reliable and is offered as an aid to help in the selection of Thomas products. It is the responsibility of the user to determine the suitability of the product for the intended use and the user assumes all risk and liability in connection there with. Thomas does not warrant, guarantee or assume any obligation or liability in connection with this information.

Models presented in this catalog are representative of the product family. Photos of products pictured in this catalog do not necessarily represent a specific model number. To obtain further information for custom options, contact your local Thomas office.

Printed in U.S.A Form No. 850-4028 01/2018 © Gardner Denver Thomas, Inc. All rights reserved.

T +49 8141 2280 0