

ELMO RIETSCHLE | BLOWER & VACUUM TECHNOLOGY

SVT SERIES

OIL SEALED SCREW VACUUM PUMP

22 - 55 KW VARIABLE SPEED



INTRODUCING THE **NEW SVT**

THE SVT VACUUM PUMP

- THE BEST CHOICE FOR EFFICIENCY & RELIABILITY IN CENTRAL VACUUM APPLICATIONS

With over 70 years of industrial vacuum engineering expertise, the latest evolution in screw design has arrived with the new SVT range in the Elmo Rietschle S-Series. The new SVT1500, SVT2000 & SVT4000 has been developed to improve the overall performance of this tried and tested oil lubricated screw vacuum pump technology. This evolutionary design provides 50% or more energy savings when compared to other fixed speed technologies.







ADVANTAGE AT A GLANCE Our evolutionary new design offers:

Premium air end from Ingersoll Rand

- Large diameter, slow running air end for maximum performance, efficiency and reliability.
- Wide flow range (20 100%) for optimum performance with minimum power.

Ingenious and simple single oil separator vessel

- Three-stage oil-air separation.
- Ultra-high oil retention
- Simple maintenance access.

Direct coupled motor

- Premium Efficiency IE3 Motor cooled by constant speed fan for optimum cooling, even at low speed.
- Air end and motor rigidly coupled for perfect alignment & supported on 3 point anti-vibration mounts.

Thermal separation zones for reliable operation

- Two separate temperature controlled zones.
- Cool operating zone for the drive motor.
- Hotter zone for the oil circuit to help prevent moisture condensation & improve oil, filter and bearing life.









Advanced frequency converter

- Advanced PID control to maintain required vacuum level and save energy
- Reduces power close to atmospheric pressure
- Global brand for ease of support
- Optional -Additional Harmonic filters are available upon request

Color touch screen HMI

- Intuitive, simple operation
- Multiple display modes
- Intelligent communications options

High efficiency inlet filter

- Over-sized internal inlet filter for low pressure drop
- Long life even on dirty applications
- Integrated differential pressure switch, signals to HMI and communications system when filter needs cleaned or changed
- Optional A full range of suction side accessories including highcapacity cyclone dust filters, combination liquid trap/demister etc. are available

Premium acoustic enclosure

- Class leading noise reduction
- Quiet & efficient ventilation
- Compact footprint



Low cost of ownership

Proven oil lubricated screw technology

Plug & play system right out of the box

Saving precious space using 1 big machine vs several small machines for same capacity





TECHNICAL

SPECIFICATIONS

PARAMETERS	SVT 1500	SVT 2000	SVT 4000
Pumping Speed (m³/hr)	1390	1940	3605
Nominal Power (kW)	22	37	55
Ultimate Vacuum (mbarA)	3	3	6
Noise (dB(A))	76	78	75
Oil Capacity (Litres)	41	41	90
Inlet (PN10)	DN 150	DN 150	DN 200
Discharge (PN10)	DN 100	DN 100	DN 150
Max./Min. Ambient Temperature (Degree C)	46 / 2	46 / 2	46 / 2
Cooling Air Flow (m³/min)	130	130	130
Full Load Current Max @ 400V (Amps)	55	85	125
Voltage (V)	400 ± 10%	400 ± 10%	400 ± 10%
Frequency (Hz)	50	50	50
Total Weight (kg)	1550	1650	3113
Dimensions (mm) L x W x H	2040 x 1360 x 1650	2040 x 1360 x 1650	2550 x 1850 x 1950







TYPICAL

APPLICATIONS



FOOD & BEVERAGE CAN MANUFACTURING AND DECORATING LINES

Vacuum is used in multiple processes, mostly for holding and pick & place

CONTAINER GLASS MANUFACTURING

Vacuum is applied to the bottle mould at the same time as internal pressure to improve accuracy and reduce wall thickness

HOUSE VACUUM IN ELECTRONICS INDUSTRY

Vacuum is used for holding, lifting, packaging etc

PRODUCT **BENEFITS**

Energy Saving

By combining a reliable, highly efficient vacuum pump with variable speed drive and accurate control, the SVT will maximise energy savings by ensuring the correct vacuum level and flow are maintained and no more. Excess vacuum causes increased volume flow, needing more pumping speed and more energy. Savings of 50% or more are possible when compared to other fixed speed technologies.

Low Maintenance Costs

With an oversized integrated inlet filter and long life oil and separator, all easy to access and change when needed, the maintenance cost of the SVT is kept to a minimum.

Water Saving

Water is becoming an expensive resource, both at the supply and disposal side. The SVT needs no water. When compared to a liquid ring vacuum pump, the SVT will use 30-50% less energy and no water.

Simple Installation

The SVT is a truly Plug & Play machine. Simply position on a level rigid surface, connect power and the vacuum connection and it's ready to go. The intuitive HMI controller makes parameter setting very simple and the multi protocol communications make it easy to integrate with factory control and monitoring systems.

SINGAPORE

Gardner Denver Pte Ltd 42 Benoi Road Singapore 629903 Republic of Singapore Tel: +65 6861 1555

MALAYSIA

Ingersoll-Rand Malaysia Co Sdn Bhd Central Branch Office Lot 4881, Jalan SS 13/2 Subang Jaya 47500 Selangor Malaysia

Tel: +60 3 5633 3322 Fax: +60 3 5634 5911

INDONESIA

PT Ingersoll Rand Indonesia Pondok Indah Office Tower 2, 16th Floor, Suite 1601 Jl. Sultan Iskandar Muda Kav. V TA Pondok Pinang, Kebayoran Lama, Jakarta 12310

Tel: +62 21 7592 2828 Fax: +62 21 7592 2827

PHILIPPINES

Ingersoll-Rand Philippines Inc Bays 8 and 9 ECH Plaza No. 8006 Drive A. Santos Avenue Barangay BF Homes 1, Sucat, Parañaque City NCR, Philippines Tel: +63 2 8826 3019

THAILAND

Gardner Denver (Thailand) Co., Ltd. 36 Soi Bangna-Trad23 Bangna-Trad Rd. Kwang Bangna, Khet Bangna Bangkok Thailand 10260 Tel: +66 2396 1134

Fax: +66 2396 1136

VIETNAM

Ingersoll-Rand Vietnam 9th Floor, No 106 Nguyen Van Troi Street Ward 8, District Phu Nhuan Ho Chi Minh City, Vietnam

Tel: +84 28 3997 7428 Fax: +84 28 3997 7426



Elmo Rietschle South East Asia www.gardnerdenver.com/elmorietschle sales.sg@irco.com