
Bronze Pedestal Rotary Gear Pumps

N13HD Series

Dimensions



NBR = Acrylonitrile-Butadiene PTFE = Polytetrafluorethylene FKM = Fluoroelastomer




Visit www.oberdorferpumps.com to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.

N13HDSeries.122014



1 1/2" NPT Ports




Seal Options								
Model	Se	Conversion						
	Туре	Material	Kit No.					
N13HDP	Packing	Acrylic-Graphite	11021					
N13HDL	Lip	FKM-PTFE	11023					
N13HDM	Mechanical	NBR-Ceramic	11025					
N13HDP-1	Packing	PTFE	11022					
N13HDLS3	Lip	NBR	11024					
N13HDLS7	Mechanical	FKM-Ceramic	11026					
N13HDPMS8	Mechanical	EPDM	TBD					

FEATURES:

- All Bronze Castings and Stainless Steel Shafts
- Sealing Arrangement Interchangeable in Field with Proper Kit
- Outboard Ball Bearing Support for Belt Drive Applications
- Self Lubricating Carbon Bearings
- Electric Clutch (Options)


SERVICE WEAR FACTORS:

Speed - High speed accelerates wear. For longer service life, keep speed as low as possible. Pump speeds above



Bronze Pedestal Rotary Gear Pumps N13HD Series

PERFORMANCE: CAPACITY WATER AT 70°F



900 RPM not recommended except for intermittent duty and pressures below 100 psi.

Pressure - High pressure accelerates wear. For longer service life keep pressure as low as possible.

Liquid Temperature - High temperature accelerates wear. Keep as close to room temperature as possible.

Liquid Contamination - Impurities like fine abrasive silt or sand accelerate wear. Keep liquid as clean as possible.

Liquid Lubricity - Lubricants increase service life many fold. Use lubricant additives whenever possible.

Noise - Large gear pumps are inherently noisy due to metal to metal gear contact. Make installations far removed from offices or other relatively quiet people areas. Some noise reduction can be realized by lowering pump speed and use of isolation mounts and lines,

Bronze Pedestal Rotary Gear Pumps N13HD Series

not justify the effort and expense.

Drive & Alignment - Direct drive is the recommended drive arrangement. This pump is suitable for belt drive applications without needing pillow block bearings to achieve acceptable pump life. Correct alignment is absolutely essential for satisfactory pump life. Recheck alignment after piping has been connected to the pump. Electric clutch versions available.

SEAL CONVERSION KITS:


Seal conversion kits, illustrated (on back) are de-

usually the small amount of noise reduction achieved does signed for quick removal and replacement. In each case, seal housings are fastened to pump bodies by means of 2 bolts, item 13. IMPORTANT - before attempting to remove a seal housing containing seal components by sliding them off the pump shaft, be sure to unlock the 2 set screws locking the ball bearing inner race to the pump shaft. The ball bearing is identified as item 20. Also, before attempting to slide the seal housing from the pump shaft, remove all burrs, scale, and projections that could be formed by fretting corrosion.

	1	2	3	4	5	6	7	8	9	10	11	12	13
	Cover	Screw	Snap Ring	O-Ring	Bearing	Drive Gear	Drive Shaft	ldle Shaft	ldle Gear	Body	O-Ring	Packing Ring	Screw
Model	Qty. 1	Qty. 8	Qty. 4 or 5	Qty. 1	Qty. 4	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 4	Qty. 2
N13HDP	9333NN5N	5393	7651 (4)	9797-158	5108	9854	7570	7653	9855	9332NH7N	6515	7624	6827
N13HDP-1	9333NN5N	5393	7651 (4)	9797-158	5108	9854	7570	7653	9855	9332NH7N	6515	7450	6827
N13HDL	9333NN5N	5393	7651 (4)	9797-158	5108	9854	7570	7653	9855	9332NH7N	9797-224	N/A	6827
N13HDLS3	9333NN5N	5393	7651 (4)	9797-158	5108	9854	7570	7653	9855	9332NH7N	6515	N/A	6827
N13HDM	9333NN5N	5393	7651 (5)	9797-158	5108	9854	7570	7653	9855	9332NH7N	6515	N/A	6827
N13HDMS7	9333NN5N	5393	7651 (5)	9797-158	5108	9854	7570	7653	9855	9332NH7N	9797-224	N/A	6827
N13HDMS8	9333NN5N	5393	7651 (5)	9999-158	5108	9854	7570	7653	9855	9332NH7N	6515	N/A	6827

	14	15	16	17	18	19	20	21	22	23	24	25	26	
	Nut	Gland	Screw	Seal Housing	Lip Seal	Snap Ring	Ball Bearing	Key	Lip Seal	Seal Assy	Dowel Pin	Тад	Tag Screw	Repair Kit
Model	Qty. 2	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 1 or 2	Qty. 1	Qty. 3	Qty. 1	Qty. 1	Qty. 2	Qty. 1	Qty. 2	
N13HDP	8395	7451	9905	7449	6710	7372 (2)	7368	6518	N/A	N/A	8597	9344	9345	11009
N13HDP-1	8395	7451	9905	7449	6710	7372 (2)	7368	6518	N/A	N/A	8597	9344	9345	TBD
N13HDL	N/A	N/A	N/A	7365	N/A	7372 (1)	7368	6518	7262	N/A	8597	9344	9345	11011
N13HDLS3	N/A	N/A	N/A	7365	N/A	7372 (1)	7368	6518	6500	N/A	8597	9344	9345	11012
N13HDM	N/A	N/A	N/A	7365	N/A	7372 (1)	7368	6518	N/A	32315	8597	9344	9345	11013
N13HDMS7	N/A	N/A	N/A	7365	N/A	7372 (1)	7368	6518	N/A	32372	8597	9344	9345	11014
N13HDMS8	N/A	N/A	N/A	7365	N/A	7372 (1)	7368	6518	N/A	33335	8597	9344	9345	TBD

Exploded View



						7	17
	Clutch Drive Options		Clutch Coil	Clutch Assembly	Pump Repair Kit	Drive Shaft	Seal Housing
Model						Qty. 1	Qty. 1
N13HDM-E12	Gear Pump, Mechanical Seal with 12V Clutch	7227	7224	32238		9168-1	9169-1
N13HDM-E24	Gear Pump, Mechanical Seal with 24V Clutch	7227	9902	33066	12029	9168-1	9169-1
N13HDM-E32	Gear Pump, Mechanical Seal with 32V Clutch	7227	7225	32239		9168-1	9169-1

Repair kit contains 3, 4, 5, 6, 7, 8, 9, 11, 12, 18, 22 & 23



