

BIG-LOCK SYSTEM FLOW RATES

	CU FT/MIN				
	70 MM	90 MM	115 MM	168 MM	220 MM
100 PSI	948	1955	3844	10078	20944
125 PSI	1064	2162	4205	11194	23169
150 PSI	1169	2364	4591	12153	25279
220 PSI	1417	2937	5568	14740	30418

Above flow rates are based on straight line flow allowing for a 1 psi pressure drop per 100 ft over pipe and couplings. For loop systems, flow rates are doubled, i.e. 90 mm tubing at 100 psi flows 3910 cfm