## **COMPRESSOR DATA SHEET**

Federal Uniform Test Method for Certain Air Compressors Not Applicable

Gardner

## **Rotary Compressor: Fixed Speed MODEL DATA - FOR COMPRESSED AIR** Manufacturer: 1 **Gardner Denver** L250-340hp-100psi 1/4/2021 Model Number: Date: 2 Х Water-cooled Air-cooled Type: Screw Х # of Stages: **Oil-injected** Oil-free 1 Rated Capacity at Full Load Operating Pressure a, e acfm<sup>a,e</sup> 3\* 1466.1 Full Load Operating Pressure <sup>b</sup> psig<sup>b</sup> 100 4 Maximum Full Flow Operating Pressure <sup>c</sup> psig<sup>c</sup> 5 110 Drive Motor Nominal Rating 6 340 hp Drive Motor Nominal Efficiency 7 96.2 percent Fan Motor Nominal Rating (if applicable) 8 3.0 / 5.4 hp Fan Motor Nominal Efficiency 9 86.7 / 86.8 percent Total Package Input Power at Zero Flow<sup>e</sup> kW<sup>e</sup> 10\* 75.9 Total Package Input Power at Rated Capacity and 11 kW<sup>d</sup> 262.43 Full Load Operating Pressure<sup>d</sup> Specific Package Input Power at Rated Capacity 12\*17.90 $kW/100 cfm^{e}$ and Full Load Operating Pressure

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Compressed Air & Gas Institute	Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
	$\underline{m^3 / \min}$	$\underline{\mathrm{ft}^3}$ / min	%	%	%
Member	Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
	0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
	1.5 to 15	53 to 529.7	+/- 5	+/- 6	
ROT 030.2	Above 15	Above 529.7	+/- 4	+/- 5	
12/10 Deer 2 This formand data large					



12/19 Rev 3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: L160-290C