



**HOFFMAN**




**LAMSON**

by Gardner Denver

GENUINE OEM PARTS FOR HOFFMAN & LAMSON BLOWERS

# QUICK SHIP PARTS





## HOFFMAN® & LAMSON® OEM Parts QUICK SHIP PROGRAM

You have a HOFFMAN & LAMSON blower for a reason, keep it that way with certified, OEM parts, available in stock, and direct to your door in 48 hours or less. Every part is HOFFMAN & LAMSON CERTIFIED™ and built to our legendary quality standards, using the latest designs for optimum efficiency and reliability. Performance is guaranteed and backed by a factory warranty.

Some companies claim to offer parts for our products, but they do not reflect the same scrutiny as HOFFMAN & LAMSON certified OEM parts. There is no guarantee of precise fit, durability or finest materials. Substandard parts can result in added long term costs from reduced operational performance or increased downtime and additional repairs.

Only genuine HOFFMAN & LAMSON CERTIFIED parts can reliably meet the performance standards of the original blower design.

**FOR THE QUALITY, RELIABILITY, AND PERFORMANCE YOU EXPECT AND YOUR OPERATION DEMANDS, YOU NEED HOFFMAN & LAMSON.**

## BEARING KITS

HOFFMAN & LAMSON uses bearings and parts made from the finest components available to ensure continued durability. Everything required for a complete bearing replacement is included in this kit, which is available direct to your door in just 2 days.

- Complete kit - no missing parts
- Vacuum sealed
- Huge dedicated parts inventory for quick delivery of all bearing kits

2 DAY QUICK SHIP




## BEARING HOUSINGS

HOFFMAN & LAMSON bearing housings are machined to designed tolerances, and all current designs are ready to ship direct to your door in just 2 days.

- Includes lip seals or seal closures
- Drilled and tapped for RTD temperature probes and other necessary connections

2 DAY QUICK SHIP



## SEAL KITS

HOFFMAN & LAMSON seals have gone through many generations of design to provide the best performance possible with today's technology.

- Serial number tracking ensures most recent part design changes
- Huge dedicated parts inventory for quick delivery
- Labyrinth or carbon ring seals available

2 DAY QUICK SHIP




## IMPELLERS

Impellers are the heart of the blower. To achieve proper performance and efficiencies, HOFFMAN & LAMSON original impellers are the logical choice for replacement. Contact customer service or your local representative to select the impeller type and configuration that will deliver optimum performance and efficiency for your HOFFMAN & LAMSON machine.

- Cast and fabricated impellers
- Multiple vane configurations
- Baked phenolic coated impellers available

2 DAY QUICK SHIP



## VACUUM HOSES, TOOLS & ACCESSORIES

Whether you have a HOFFMAN, LAMSON, or INVINCIBLE vacuum system, we have the hose, tools, and accessories to handle the most demanding industrial vacuum application efficiently.

- Commercial and industrial heavy-duty floor rods and tools
- Durable hoses for almost any application
- Thousands of parts in stock

Other available vacuum products include:

- SmoothFlow tubing and fittings
- HEPA and bag filters
- Separators

2 DAY QUICK SHIP



# HOFFMAN® & LAMSON® Products & Systems



## HOFFMAN & LAMSON Multistage Centrifugal Blowers

HOFFMAN & LAMSON Multistage Centrifugal Blowers are the ideal solution for processes that require uniform pressure, pulse-free flow, and oil-free operation. With designs optimized for 60 and 50 Hz markets, we offer efficient performance backed by a history of reliable operations.




## HOFFMAN REVOLUTION™ High Speed Centrifugal

The HOFFMAN REVOLUTION High Speed Centrifugal Blower utilizes advanced centrifugal engineering technologies that deliver up to 45% energy savings, provide increased reliability with little or no maintenance, and come factory pre-wired and tested in an ergonomically designed sound enclosure for plug-and-play operation.



## Controls & Energy Management

Considering an efficiency upgrade? HOFFMAN & LAMSON upgrades and High Speed Centrifugal Blower solutions deliver increased efficiency and improved reliability for your water and wastewater treatment applications.



## Support, Service & OEM Parts

Restore blower performance and maintain system reliability with HOFFMAN & LAMSON OEM Service, support, and parts - available through our global network of HOFFMAN & LAMSON CERTIFIED™ Service & Distribution Centers.



**LAMSON**


**Gardner Denver Nash, LLC**

PO Box 130  
Bentleyville, PA 15314 USA  
800-553-NASH  
+1 724 239 1500

[info.hoffmanlamson@gardnerdenver.com](mailto:info.hoffmanlamson@gardnerdenver.com)  
[www.HoffmanAndLamson.com](http://www.HoffmanAndLamson.com)

©2017 Gardner Denver Nash, LLC Printed in U.S.A.  
CF-A-1-460 3rd Ed. 08/17

**Gardner  
Denver**

 Please recycle after use.