

D2000 - PTFE | SWIVEL JOINT



Swivel joints for heavy duty special applications

The swivel joint D2000 - PTFE is a variant of the basic form. It is internally lined with PTFE and is equipped with a special seal. Therefore it is suitable for extremely aggressive

The ball tracks are encapsulated by two Orings. Neither dirt from the outside nor product from within (in case of leakage) can reach the ball track.

Should the main seal fail, leakage is indicated through the leak detection port. This port is PTFE sleeved. Thus contact of product with carbon steel components is prevented.

The bearing module with his deep hardened ball race and the special designed seals guarantee a reliable and long life working swivel joint. The bearing module and the seals can be easily replaced. All carbon steel parts could be made of stainless steel.

The D2000 - PTFE swivel joint is equipped with special flanges. The connection flanges for the pipes are included in the swivel joint order. These flanges are welded to the pipes and then PTFE lined as an assembly.

assist@emcowheaton.com








D2000 - PTFE | SWIVEL JOINT

TECHNICAL DATA D2000 - PTFE								
Size *DN	Material	Seal material	Allowable internal pressure (gauge pressure)		Allowable temperature range**			
			operational	test pressure				
50, 80, 100, 150, 200	carbon steel steel PTFE lined	PTFE	10 bar	15 bar	-10 °c to +150 °c			

^{*} Larger sizes are available.

^{**} Temperature range might be restricted due to seal material.

DIMENSIONS AND WEIGHTS (METRIC) D2000 - PTFE							
Size	Α	Bolts	Weight				
DN 50	176	8 × M 8	9 kg				
DN 80	205	8 × M 8	12 kg				
DN 100	256	12 × M 10	18 kg				
DN 150	on request	on request	on request				
DN 200	on request	on request	on request				
Dimensions and weights for larger swivel joints are available on request							



- 1. flange
- 2. Spacer ring
- 3. Bearing modul D2000
- 4. flange screws
- 5. Swivel joint seal
- 6. Screws for connecting flange
- 7. Socket set screw
- 8. leakage control