

FLOMAX 35 SS

4" x 3" 316 Stainless Steel, Self-Priming, Centrifugal Pump

The 316 Stainless Steel FLOMAX® 35 provides excellent chemical compatibility and corrosion resistance for "hard-to-handle" aggressive fluids making it ideal for numerous agricultural, industrial and marine applications. The pump is equipped with a standard viton flapper, priming chamber fill-plug, and a 4" NPT Suction Flange which offers improved suction lift capabilities at the higher flow range. The discharge port is 3" ANSI 150 # Class Flat Flange. The standard mechanical seal is carbon/ceramic/viton/stainless steel. Consult factory for optional seals. Two basic PumPak styles allow the FLOMAX® 35 self-priming centrifugal pump to fit standard Nema "C" electric motor frames, engines or the standard MP pedestal. The PUMPAK is completely assembled and can be mounted to a standard motor in minutes. Applications include: AG Fertilizer transfer, Chemical transfer, Diesel Exhaust Fluid (DEF) transfer and R.O. water transfer.



SPECIFICATIONS:

Flow Up to 500 GPM

Impeller 316 SS, Semi-Open, Balanced

Seal Carbon/Ceramic/Viton

Mounting Options PumpPak, Pedestal, Engine , Electric


Motor: -256TC -286TSC

Discharge 3" NPT 150 # Class Flat Flange


Application


- Agricultural
- Industrial
- Marine

FM35, 4x3 7.0 Impeller



FLOMAX 35 SS





FLOMAX 35 SS

3* NOT Discharge Class #150 18.05 18.05 10.97 10.97 10.584 10.591 10.97 10.584 10.591 10.97 10.585 10.97 10.985 10.97 10.985 10.97 10.985 10