





Gardner
Denver

POSITIVE DISPLACEMENT BLOWERS
ROTARY VANE COMPRESSORS | VACUUM PUMPS

Vacuum Truck Products



Offering the **Most Comprehensive Line** of Vacuum Truck Products

VEHICLE TYPE	APPLICATION	
<p>Pull-Behind Vacuum Trailers</p>	<ul style="list-style-type: none"> ■ Trenching ■ Portable Restroom Cleaning ■ Grease Trap Cleaning ■ Vacuum Excavation 	
<p>Pumper Trucks</p>	<ul style="list-style-type: none"> ■ Septic Tank Cleaning ■ Hydraulic Fracturing Water Collection 	
<p>Municipal Trucks</p>	<ul style="list-style-type: none"> ■ City Sewer Trucks 	
<p>Hydro-Excavation Trucks</p>	<ul style="list-style-type: none"> ■ Hydro-Excavation ■ Oil Field Process Removal/Storage 	



PRODUCT MODELS

- Sutorbilt Legend
- RBS 45
- HeliFlow
- RB-DV 45



- RFL 100
- RFL 102
- RFW
- RB-DV 45



- TriFlow 825
- TriFlow 825-MV



- RB-DV 145



Pull-Behind Vacuum Trailers

Ideal Applications

- Industrial Vacuum Excavation
- Potholing Utilities
- Drill Mud Cleanup
- Safer Digging Around Utilities





Sutorbilt Legend

- DSL or Grease Lube Options
- Vacuum up to 15 inHg
- Bi-Lobe Rotor Profile



RBS Series

- DSL Lubrication
- Vacuum up to 16 inHg
- Robust Design
- Tri-Lobe Rotor Profile



HeliFlow

- DSL Lubrication
- Vacuum up to 16 inHg
- Helical Tri-Lobe Rotor Profile
- Reduced Pulsations = Lower Noise & Higher Reliability




RB-DV

- Deeper Vacuum—can run continuous up to 27 inHg
- Easy Maintenance—no wearing parts
- Patented air injection system for cooler temps, noise reduction, efficiency, & ease of installation

LOW VACUUM
up to 16 inHg

HIGH VACUUM
up to 27 inHg


Fixed Axle Pumper Trucks



Standard upright installation



Side-mount installation



The RFL 102 features top-mounted reverse flow and non-return valve.



Ideal Applications

- Restaurant Grease Traps
- Septic Tanks
- Holding Pits
- Cesspool Pumping
- Oil Well Service
- Sludge Removal



RFL 100

- Continuous Vacuum up to 24 inHg
- Airflow up to 412 cfm
- Most Durable Pump in Its Class



RFL 102

- Continuous Vacuum up to 24 inHg
- New Side-Mounted Lubrication Tank, Remote-Mount Optional
- More Compact Suction Filter Saving Space



RFW

- Intermittent Vacuum up to 27 inHg (24 inHg Continuous Vacuum)
- Water-Cooled Unit
- Fast Evacuation Times
- Multiple Drive Options Available
- Compact Mounting Design



RB-DV 45

- Deeper Vacuum—can run continuous up to 27 inHg
- Easy Maintenance—no wearing parts
- Patented air injection system for cooler temps, noise reduction, efficiency, and ease of installation

HIGH VACUUM
up to 27 inHg

Municipal Trucks

Ideal Applications

- Sewer Cleaning
- Storm Sewers
- Water Treatment Plants
- Municipal Water Departments
- Cleaning & Washing





TriFlow 825

- Vacuum up to 18 inHg
- It's efficient: up to 27% more efficient than a similar size bi-lobe blower installation

ROUGH VACUUM
up to 18 inHg



TriFlow 825-MV

- Innovative Design
- Class-exclusive 20 inHg
- Air Injection System for cooler operating temperatures and ease of installation

ROUGH VACUUM
up to 20 inHg



RB-DV



- Deeper Vacuum—Can run continuous up to 27 inHg
- Easy Maintenance—No wearing parts
- Patented air injection system for cooler operating temperatures, noise reduction, and ease of installation

HIGH VACUUM
up to 27 inHg

Hydro-Excavation Trucks

RB-DV is Fuel Efficient

Tri-Lobe design with patented air injection is fuel efficient, putting more money in the operator's pocket.



Patented & Unique Air Injection

- Offers cooler operating temperatures
- Won't overheat on a dead head
- Best-in-class noise reduction



No Cast-In Manifolds

- Reduces equipment weight & space
- Easy to install
- Less equipment weight
 - = More loads (load capacity)
 - = More money savings per load!



Performance

- Continuously Runs at 27 inHg
- Offers Vacuum Level up to 28 inHg on a Dead Head
- Offers Flows from 494-6,200 CFM

Ideal Applications

- Industrial Combination Trucks
- Hydro Excavation
- Potholing Utilities
- Oil Collection
- Oil Field Water
- Grit Recovery Trailers

RB-DV

- Deeper Vacuum—Can run continuous up to 27 inHg
- Easy Maintenance—No wearing parts
- Patented air injection system for cooler operating temperatures, noise reduction, and ease of installation

HIGH VACUUM
up to 27 inHg

The leader in every market we serve
by continuously improving all business processes
with a focus on innovation and velocity

**Gardner
Denver**[®]

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-376-8181

www.gardnerdenver.com/gdproducts



©2017 Gardner Denver, Inc. Printed in U.S.A.
GDT-VAC-TRUCKS 3rd Ed. 3/17

Please recycle after use.