## **COMPRESSOR DATA SHEET**



## In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

## **Rotary Compressor: Variable Displacement**

1	Manufacturer: Gardner Denver			
	Model Number: SAVG2-75hp-125psi	i	Date:	01/04/21
2	X Air-cooled Water-cooled		Type:	Screw
	X Lubricated Oil Free		# of Stages:	1
*	Full Load Operating Pressure <sup>b</sup>	125		psig
4	Drive Motor Nominal Rating	75	hp	
5	Drive Motor Nominal Efficiency	95.4	percent	
5	Fan Motor Nominal Rating (if applicable)	3	hp	
7	Fan Motor Nominal Efficiency	82.5	percent	
	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>	
	69.3	342	20.26	
*	58.3	267	21.84	
	48.1	202	23.81	
	43.8	164	26.71	
	43.3	132	32.80	
*	Total Package Input Power at Zero Flow <sup>c, c</sup>	d 15.6	kW	
0	Isentropic Efficiency at Full Flow Rated Capacity and Full Load Operating Pressure	74.1	74.1 %	
	35.00			
	30.00			
	la Maria			
	25.00 <b>Specific Power</b> 20.00 <b>CHM</b>			
1				
	15.00			

Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator Consult CAGI website for a list of participants in the third party verification program: <u>www.cagi.org</u>



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%,
  - manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

ROT 032.1

	Volume Flow Rate	Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power	
$\underline{m^3 / \min}$	$\underline{ft^3} / \underline{min}$	%	%	%	
Below 0.5	Below 17.6	+/- 7	+/- 8		
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	., 10,0	
Above 15	Above 529.7	+/- 4	+/- 5		

6/20. Rev2 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: SAV75-100G2B