## **COMPRESSOR DATA SHEET**



## In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

**Rotary Compressor: Variable Displacement** 

MODEL DATA - FOR COMPRESSED AIR								
1	Manufacturer: Gardner De	nver						
	Model Number: SAV-200hp-EAUDD-100psi		Date:	01/04/21				
2	X Air-cooled Water-cooled		Type:	Screw				
	X Lubricated Oil Free		# of Stages:	1				
3*	Full Load Operating Pressure b	100						
4	Drive Motor Nominal Rating	iting 200		hp				
5	Drive Motor Nominal Efficiency	95.8	percent					
6	Fan Motor Nominal Rating (if app	licable) 5	5 hp					
7	Fan Motor Nominal Efficiency	89.5		percent				
8*	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>		Specific Power (kW/100 acfm) <sup>d</sup>				
	179.3	974		18.41				
	167.1	877	19.05					
	144.4	682	21.17					
	125.5	487		25.77				
	119.9	390		30.74				
9*	Total Package Input Power at Zero			kW				
10	Isentropic Efficiency at Full Flow I Capacity and Full Load Operating			%				
11	35.00  30.00  25.00  20.00  15.00							
	Note:	Capacity (ACFM)  Graph is only a visual representation of the data i xis Scale, 10 to 35, + 5kW/100acfm increments if nec X-Axis Scale, 0 to 25% over maximum capacity		00 1200				

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator Consult CAGI website for a list of participants in the third party verification program: <a href="www.cagi.org">www.cagi.org</a>



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$\underline{\mathbf{m}}^3 / \underline{\mathbf{min}}$	<u>ft<sup>3</sup> / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	1, 10,0
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 032.1

Configurator: EAU99AB