

HYDRAULIC DRIVE COOLING SYSTEMS

# MH5 Series Hydrapak®







### MH5 Series Hydrapak

The MH5 Hydrapak is a compact, lightweight, highly efficient hydraulic control system aimed for use in high horsepower and high flow mobile hydraulic drive systems. Operating with virtually no maintenance, this easy install system weighs hundreds of pounds less than a conventional reservoir type system.

#### Features & Benefits

- Durable, heavy-duty stainless steel mainframe
- Designed to withstand vibration, road shock, torsional and thermal stress
- Multi-ported design reduces the need for hoses, fitting & external connections

### MH5 Hydrapak

- Flow rate to 60 gpm
- Pressure rated to 3000 psi
- 4.4 gallon reservoir
- Weight: 94 lbs. dry


#### **Optional Equipment:**

- Oil heater kit
- Diagnostic test point kit
- Pressure cap
- Bulk feed specification
- Non-Vented cap for cylinder applications


#### Applications

- Crude Oil Transports
- LP Gas Transports
- LP Gas Bobtails
- Food & Chemical Transports
- Bulk Feed
- Lube Trucks
- Maintenance Trucks
- Hydraulic Winch Drives
- Utility Equipment
- Agriculture Equipment
- Mining Equipment
- Water Trucks
- CO<sub>2</sub> Delivery Trucks
- Vacuum Trucks
- Live Floor

#### DIMENSIONS: MH5 HYDRAPAK



#### PERFORMANCE: MH5 HYDRAPAK\*



\*Performance curve is for reference only. Actual performance may vary based on system design, environment, and maintenance.



## The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



#### Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-376-8181 www.gardnerdenver.com/gdproducts

©2019 Gardner Denver, Inc. Printed in U.S.A. GDT-MH5-HP 2nd Ed. 8/19





Please recycle after use.