Customer Focused Aftermarket Solutions

MULTISTAGE CENTRIFUGAL BLOWERS




Aftermarket Product Menu

SUPERIOR SERVICE AND GENUINE HOFFMAN & LAMSON PARTS









Field Services

- Warranty Renewal Programs
- Predictive Maintenance Programs
- Start-up
- Certified Vibration Analysis
- Laser Alignment
- Troubleshooting
- Training
- Diagnostics
- Testing

Products

- Genuine Factory Parts
 - New Blower
 - Components
 - Factory Certified
 - Reconditioned
 Components
 - Control Components
- Factory Reconditioned Blowers
- Blower Lubricants
- Blower Accessories
- Blower Controls
- Buy-backs

Factory Services

- Worldwide Blower Repair
- Rotor Re-balance
- Machine Component Forensic Inspection
- Testing
 - ASME
 - Gas
 - Mechanical
 - Hydrostatic
 - Overspeed
 - Dye Penetrant
- In-House Blast Cleaning and Specialty Coatings

Engineering Services

- Blower Reconfiguration for Performance Changes
- Performance Curves
- Amp Curves
- System Consulting
- Technical Product Support
- Custom Application Engineering
- Seismic Calculations
- Product Upgrades
- Instrumentation Upgrades





One-Year Factory Warranty

TO PROTECT YOUR INVESTMENT

All Hoffman® and Lamson® Factory Service products and services are backed by our One-Year Factory Warranty. Since our inception over 100 years ago, Hoffman & Lamson have provided quality industrial products backed by superior service and aftermarket support. Today, the tradition continues, as Hoffman & Lamson products are supported by an international team of engineers and service professionals who know how to keep your blowers running at maximum efficiency. Our factory-trained service technicians are available for on-site/on-demand repair service, training, troubleshooting and consulting. We service Hoffman & Lamson blowers, as well as most other brands of centrifugal blowers.

For added assurance, we offer our exclusive Hoffman & Lamson Warranty Renewal Program. Along with our superior service comes superior parts. "Unauthorized" repair shops have been known to use reconditioned parts for blower repairs, resulting in a short repair life. Improper and non-factory approved lubricants may also be incorrectly specified by unauthorized repair shops or individuals. We use only genuine Hoffman & Lamson factory-certified replacement parts and superior lubricants specifically formulated for optimal blower performance.

Protect your investment with confidence. Go with the Hoffman & Lamson team of service and customer service professionals for all of your after-the-sale service and aftermarket needs.



Products

ORIGINAL EQUIPMENT QUALITY

Remanufactured Blowers/Exhausters

Hoffman & Lamson offer a wide range of factory remanufactured blowers and exhausters available for immediate shipment. Remanufactured blowers are built to the same exacting standards as our new machines, rigorously tested and carry the same factory warranty. If we do not have a particular remanufactured blower in stock, we can build one to match your specific application. Remanufactured blowers and exhausters offer an excellent, cost-effective alternative to new machines, and they are ideal for short-term projects, spares and even permanent installations.

Why Choose Remanufactured?

- Cost effective
- Same warranty as new
- All Genuine Factory Certified Parts
- Ideal for short-term projects
- Emergency Solutions
- Same specifications as new, incorporating latest design upgrades



Remanufactured Models Available	
Hoffman® Series	Lamson® Series
42	310
741/384	510/550
751	810/850
383	1210/1250
761	1260
791	1400
671	1850/1870



Buy-Back Program

Do you have old blowers that have been abandoned or are not being used? We will buy back many popular models and pick them up at your location. Contact the Hoffman/Lamson service group or your local representative.

Genuine Hoffman & Lamson Parts and Lubricants

Keep your Hoffman & Lamson investment running smoothly for years with Genuine Hoffman & Lamson parts and lubricants from your local Authorized Hoffman & Lamson Sales and Service Representative. These professionals provide you the expert guidance you appreciate for sales assistance, installation support and maintenance advice. Whether you're replacing a typical wear component or changing the grease or oil, nothing outperforms genuine Hoffman & Lamson factory parts and lubricants. They're specifically engineered for superior performance and extended life of your blower/exhauster.





Factory Services

LOCATIONS WORLDWIDE



In-House Sandblasting and Heresite Coatings and Heresite Coatings.



Rotor Balancing



ASME PTC-10 Testing

Hoffman & Lamson Factory Repairs

Hoffman & Lamson offer complete repair capability worldwide. Factory repair specialists completely disassemble, clean, inspect, re-balance and repair your blower to its original factory specifications. All repairs are done using genuine factory certified parts. When repairs are complete, each machine is rigorously tested to factory standards and covered by a new product warranty.

Hoffman & Lamson Factory Field Service

Regionally located Factory Service Technicians can be dispatched to your facility for on-site repairs, troubleshooting and other factory services, such as laser alignment, vibration analysis, operator and maintenance training and warranty renewal services.







Field Services

Preventive Maintenance Agreement/Warranty Renewal Program

- Exclusive to Hoffman & Lamson
- Comprehensive set of service and maintenance procedures
- Designed to return your blower to a rewarrantable condition
- Provides increased reliability and performance

Work Scope

- On-site inspection
- Work performed on-site with factory-trained technicians
- Complete inspection and repair report provided
- Worn or defective parts replaced or repaired with genuine factory certified parts
- New equipment warranty is re-initiated










Benefits

- Lower overall repair and reinstallation cost
- Quicker return of unit to service
- On-site equipment and operator training



Engineering Services

In addition to the many field services, we offer engineering services performed by an experienced, dedicated staff to provide amp curves, performance curves and seismic calculations. They are also available for general consulting and technical support. In most cases, they can also reconfigure your Hoffman or Lamson blower/exhauster to meet the precise requirements of any application or process changes. Need more airflow, pressure or vacuum? Our application engineers can determine what modifications would be needed, and our specialists will add the necessary stages and impellers to meet your needs. The modified blower will be built to factory specifications with genuine Hoffman or Lamson parts and will receive a one-year warranty like a new blower.













Gardner Denver

www. Hoffman and Lamson. comin fo. hoffman lams on @gardner denver. comin for the compact of t

Gardner Denver Nash PO Box 130 Bentleyville, PA 15314 USA New Equipment Sales: (800) 543-7736 Aftermarket Parts Sales: (800) 982-3009

Phone: +1 724-239-1500 Fax: +1 724-239-1502







Specifications subject to change without notice.

