

v & w series | 15 hp reciprocating compressors Pump Model WTS

Customized Solutions

Champion oil-less compressors are designed to meet the most precise standards for compressed air purity in industrial and medical facility applications. With advanced design features and a system that combines quality, durability and state-of-the-art lubrication technology, the V & W Series offers freedom from oil...freedom from maintenance...freedom from noise...freedom from worry.

Standard Features

- Totally dry crankcase
- Oil-less compressor service—"O" ring bumper eliminates end wear
- Nickel-plated, cast-iron cylinders
- Long-lasting ball bearing design
- High-grade steel valve plates and reeds
- Cantilevered crankshaft design for superior balance and long life
- Spring-isolated base
- Meets NFPA guidelines for medical air compressors
- 1-Year package warranty
- 1-Year pump warranty

Available Options

- Control panel
- Fusible disconnect switches
- Automatic tank drain
- Flexible discharge line
- Vibration isolators
- Vinyl-lined or galvanized receivers
- Water-cooled aftercooler
- Remote intake air filter/silencer
- High temperature shutdown/lag
- Compressor alarm
- Air dryer and bypass piping
- Downstream filter banks and indicator



BARE PUMP

MODEL	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLINDERS	DISPLACEMENT CFM MAX	COOLING AIR FLOW MAX CFM @ 175 PSI	HEAT REJECTION MAX BTU/HR	COOLING WATER FLOW GPM	MAX PUMP RPM
WTS	690	4.72	2.36	3	86.7	2870	30500	2	1140

SIMPLEX BASE MOUNTED UNITS

MOTOR	V & W SERIES	DIMENSIONS L × W × H	APPROX. SHIP WEIGHT	CFM DEL'Y		
HP	CIBVWA	INCHES	LBS.	50 PSIG	100 PSIG	
15	15WTS55	57.3 × 37.5 × 37.4	1180	69	56.5	

SIMPLEX TANK MOUNTED UNITS

MOTOR	TANK CAPACITY	V & W SERIES	DIMENSIONS L × W × H	APPROX. SHIP WEIGHT	CFM DEL'Y	
HP	GAL.	CISVWA	INCHES	LBS.	50 PSIG	100 PSIG
15	120	12T15WTS55	69 × 37.5 × 67	1725	69.0	56.5
15	250	25T15WTS55	92 × 37.5 × 73	2145	69.0	56.5

DUPLEX TANK MOUNTED UNITS

MOTOR	TANK CAPACITY	V & W SERIES	DIMENSIONS L × W × H	APPROX. SHIP WEIGHT	CFM DEL'Y	
HP	GAL.	CIDVWA	INCHES	LBS.	50 PSIG	100 PSIG
15 (2)	120	12TD15WTS55	88.3 × 57.3 × 60.5	3065	138	113
15 (2)	250	25TD15WTS55	84 × 67 × 72	3440	138	113

VERTICAL TWO-STAGE, CABINET ENCLOSED

MOTOR	V & W SERIES	DIMENSIONS L × W × H	APPROX. SHIP WEIGHT	CFM DEL'Y		
HP	CICVWA	INCHES	LBS.	50 PSIG	100 PSIG	
15	15EWTS55	40 × 37 × 65.8	1180	69	56.5	



1301 North Euclid Avenue Princeton, Illinois 61356 USA 866-276-4330 www.ChampionPneumatic.com

©2017 Gardner Denver, Inc. Printed in U.S.A. CRCS-VW-WTS 1st Ed. 6/17 Supersedes CR-VW-WTS 2nd Ed. 5/17



Please recycle after use.

