## **CHX Specifications**

PART NUMBER	FLOW DIRECTION	MAX FLOW SCFM	CONNECTION SIZE (FEMALE)	MAX INLET PRESSURE PSIG	CONTROL RANGE PSIG	MAX OPERATING TEMP. RANGE	SENSITIVITY	REPEATABILITY
CHX75-RL	Right to Left	75	½" NPT		0-160	-4 to 176° F -20 to 80° C	0.2% of full span	± 0.5% of full span
CHX75-LR	Left to Right	75	1/2" NPT					
CHX200-RL	Right to Left	200	1" NPT	700				
CHX200-LR	Left to Right	200	1" NPT	300				
CHX1000-RL	Right to Left	1000	2" NPT					
CHX1000-LR	Left to Right	1000	2" NPT					

PART NUMBER	А	В	С	D	E	WEIGHT
CHX75-RL	8.11"	7.28"	8.57"	7.36"	1.89"	8.40 lbs.
CHX75-LR					1.89"	8.40 lbs.
CHX200-RL					2.21"	10.45 lbs.
CHX200-LR					2.21"	10.45 lbs.
CHX1000-RL					2.78"	14.65 lbs.
CHX1000-LR					2.78"	14.65 lbs.



