

Gardner Denver

Premium compressor design & industry leading warranty

ESM 55 - 75 Fixed Speed
VS 55 - 75 Variable Speed



Reliability & efficiency
without compromise

“Lowest operational costs thanks to a 7% efficiency increase.”

Quality pays off

The ESM and VS Series from Gardner Denver

Well known in the industry for quality and reliability, Gardner Denver continuously develops the ESM and VS series achieving cutting edge performance and efficiency. The lubricated screw compressor range from 55 to 75 kW comprises of fixed speed and variable speed (VS) models. All models are optionally available with integrated heat recovery.

- ▶ **Pressure range**
5 to 13 bar
- ▶ **Volume flow**
2.10 - 14.03 m³/min
- ▶ **Motor power**
55 to 75 kW

Engineering excellence

Compressors are more than just a financial investment, they are a key component in ensuring that manufacturers, processors and operators receive consistent, high quality low cost air.

The screw compression element is the heart of the compressor and therefore Gardner Denver keeps the design and manufacture in-house, using the latest CNC rotor grinding machinery, coupled with online laser technology.

The resulting reliability and performance ensures that operating costs will remain low throughout the compressor's life.



Premium efficiency air end

The new GD6 air end ensures higher efficiency levels, by up to 5% compared to the previous one, providing fewer pressure drops, in an optimised compact design. Gardner Denver's unique design, with integrated oil filter and oil regulation valve, ensures external hoses are reduced to a minimum. The integrated air end design assures the reliability of the compressor, continuous hassle-free operation and easy servicing. Under the free Protect 10 warranty the air ends are covered up to 44,000 hours or 10 years*.


* Whichever is soonest



“Gardner Denver lubricated rotary screw compressors incorporate the very **latest technological advances** and guarantee a continuous supply of high quality compressed air.”

GD Pilot TS **innovative touch screen** compressor controller

The GD Pilot TS with its high resolution touch screen display is extremely user-friendly and self-explanatory. All functions are clearly structured in five main menus and are intuitively visual. The multilingual GD Pilot TS control system ensures reliable operation and protects your investment by continuously monitoring the operational parameters, which is essential for reducing your running costs.



Outstanding Benefits

Re-designed GD6 semi integrated airend

Optimised GD6 airend provides better performance, higher efficiency levels and lower pressure drop.

Highest efficiency levels

Up to 8% improvement.

Lowest floor space requirement

In average 8% less than comparable products in the market.

Implementation of new automatic oil regulation valve for variable speed models

Adding to the efficiency improvement.

The automatic motor lubrication is standard

It increases the bearing life and is maintenance free.

The new fine separator with just one integrated sealing

Makes maintenance easy as no o-ring replacement is required.

All doors are hinged and can be removed

Reducing the space requirements and optimising accessibility.

Premium electric motor

Standard asynchronous version IE3 or optional IE4 for even greater efficiency.

Features & functions

- Home Page – instant overview of the compressor status
- Real Time Clock – allows pre-setting of compressor starting/stopping
- Second Pressure Setting
- Integrated Cooling and Dryer Control
- Fault History Log – for in-depth analysis
- Remote Control via Programmable Inputs
- Auto Restart after Power Failure
- Optional Base Load Sequencing
- SD Card – stores several run characteristics
- iConn enabled

Trend diagrams

With the ability to display detailed system analysis in the form of trend diagrams and graphs, operating parameters can be precisely set to maximise efficiency.

- Line / Network Pressure
- Motor Speed (Variable Speed)
- On Load Hours / Total Hours Run & Average Volume Flow
- Weekly Average Volume Flow



Variable Speed Compressors

Innovative oil regulation valve

Specially designed by Gardner Denver's engineering team, this integrated valve:


- Eliminates the risk of condensate to avoid corrosion and extends oil's life time
- Depending on the working conditions improves efficiency by up to 5% for the variable speed models
- Improves low running speeds



The perfect response to individual air demands

Variable speed compressors from Gardner Denver can efficiently and reliably handle the varying air demand found in most plant air systems.

The annual cost of ownership can be significantly reduced using variable speed technology.



Add further value

Integrated heat recovery

Significant energy and costs savings can be achieved with Gardner Denver's efficient integrated heat recovery system. It can be either factory fitted or supplied as retrofit kit including all necessary pipe-work and fittings.



Motor Efficiency

As a standard, all compressors of this range are equipped with an energy efficient IE3 electric motor. To achieve even higher levels of efficiency they are optionally available with an IE4 motor.



iConn



iConn Industry 4.0 solution

The ESM and VS series is equipped with iConn as a standard. iConn is the smart, proactive real-time monitoring service that delivers in-depth and real-time knowledge on the system to our compressed air users. It enables accurate production planning and total peace-of-mind protection, generating insight and statistics that keep users informed on performance, at the same time highlighting potential issues before they become a problem.

iConn benefits at a glance

Proactive real-time monitoring with iConn for your compressed air installation, delivers many benefits:

- ✓ Real-time operating data available around the clock
- ✓ On-demand maintenance extends compressor life cycle and optimises costs
- ✓ Maximum compressor performance reduces energy consumption
- ✓ Predictive and preventative monitoring and warnings avoid expensive downtime
- ✓ Wear of compressed air components is identified early
- ✓ Reduce operating costs caused by increased pressure drop in filters and separators through late maintenance
- ✓ Identify potential savings by measuring costs and efficiency
- ✓ Optimised maintenance planning

Compressed air purification

A modern production system and process demands increasing levels of air quality, and compressed air operators need to ensure that the downstream equipment also delivers on it 100%.

The new downstream portfolio manufactured by Gardner Denver utilising the latest technology, provides an energy efficient solution at lowest life cycle costs. The same quality, performance and efficiency standards delivered by the compressors can now be enjoyed from the air treatment range.

Investment in a manufacturing site in addition to the support teams, ensures that compressed air operators don't need to worry about the quality of their compressed air – quality that is key to ensuring maximum production efficiency and investment protection.

- Water Cyclone Separators
- Compressed Air Filters
- Condensate Drain System
- Compressed Air Refrigerant Dryer
- Heatless Desiccant Dryers
- Heat Regenerative Desiccant Dryers
- Nitrogen Generator
- GD Connect 12 Multi Compressor Controller



The best investment protection you can get



Extended Warranty for GD Compressors

10 Years Warranty!

The Gardner Denver Protect 10 Warranty and Service programmes will protect you up to 44,000 hours/10 years¹. It is one of the most generous warranties available in the industry affording you total piece of mind.

Your benefits:

- The Protect 10 warranty is totally free to the compressor owner²
- The Gardner Denver authorised service provider will deliver a guaranteed quality of service
- The Protect 10 service agreement underpinning the warranty will enable accurate maintenance, budgeting and cost of ownership
- The use of genuine Gardner Denver parts and lubricants will maximise compressor life and efficiency

¹ Warranty duration is limited to 6 years/44,000 hours on the whole package, 10 years/44,000 hours on the air end. Whichever is the soonest.

² subject to Terms & Conditions

Compact design - easy installation

The small footprint reduces the space required for installation.

Easy servicing

The design of these packages ensures that the service points are readily accessible. The enclosure side doors are hinged and removable to allow complete access to all service points. The reduced number of moving parts further lowers the maintenance costs.

Gardner Denver genuine spare parts

Enjoy complete peace of mind.

Genuine Gardner Denver parts and lubricants ensure that compressed air plant reliability and efficiency is maintained at the highest standards. Gardner Denver spare parts and lubricants are distinguished by:

- Long service life, even under harshest conditions
- Minimum losses contributing to energy savings
- High reliability improves plant up-time
- Products manufactured with the strictest Quality Assurance Systems





Technical data

ESM 55 - 75 Fixed Speed Screw Compressors

Gardner Denver model	Nominal Pressure	Drive Motor	FAD ¹⁾	Noise Level ²⁾	Weight	Dimensions L x W x H
	bar g	kW	m ³ /min	dB(A)	kg	mm
ESM55	7.5	55	10.71	69	1405	1958 x 1138 x 1857
	10		9.50			
	13		8.25			
ESM75	7.5	75	13.98	72	1495	1958 x 1138 x 1857
	10		12.54			
	13		10.50			

VS 55 - 75 Variable Speed Screw Compressors

Gardner Denver model	Nominal Pressure	Drive Motor	FAD ¹⁾ Min - Max	Noise Level ²⁾ at 70% Load	Weight	Dimensions L x W x H
	bar g	kW	m ³ /min	dB(A)	kg	mm
VS55	5 - 10	55	2.50 - 10.99	69 - 72	1430	1958 x 1138 x 1857
VS75	5 - 13	75	2.10 - 14.03	72 - 74	1520	1958 x 1138 x 1857

1) Data measured and stated in accordance with ISO 1217, Edition 4, Annex C and Annex E and the following conditions:
Air Intake Pressure 1 bar a, Air Intake Temperature 20°C, Humidity 0 % (Dry).

2) Measured in free field conditions in accordance with ISO 2151, tolerance ± 3dB (A).

Global Expertise

The GD rotary screw compressor range from 2.2 – 500 kW, available in both variable and fixed speed compression technologies, are designed to meet the highest requirements which the modern work environment and machine operators place on them.



The oil-free EnviroAire range from 15 – 315 kW provides high quality and energy efficient compressed air for use in a wide range of applications. The totally oil-free design eliminates the issue of contaminated air, reducing the risk and associated cost of product spoilage and rework.



A modern production system and process demands increasing levels of air quality. Our complete **Air Treatment Range** ensures the highest product quality and efficient operation.



Compressor systems are typically comprised of multiple compressors delivering air to a common header. The combined capacity of these machines is generally greater than the maximum site demand. To ensure the system is operated to the highest levels of efficiency, the **GD Connect** air management system is essential.



gdcompressors.eu@gardnerdenver.com
www.gardnerdenver.com/gdproducts

For additional information please contact Gardner Denver or your local representative.

Specifications subject to change without notice.