

HV RS Series

hp	kW	Model	Voltage/Phase	CFM 90 PSIG	CFM 115 PSIG	CFM 150 PSIG	Noise Level (dBA)	Air Outlet NPT	Oil Cap. (Gal)	Weight (lbs.)	L (in.)	W (in.)	H (in.)	Starter	After cooler
15	11	HV11RS	200-230 or 460 3Ph	61.6	52.9	48.5	69	.75"	1.5	866	32.5	28	60	Yes	Yes
20	15	HV15RS	200-230 or 460 3Ph	80.8	71.6	60.7	70	.75"	1.5	895	32.5	28	60	Yes	Yes
25	18	HV18RS	200-230 or 460 3Ph	103.1	94.9	86.5	71	1"	2	1118	32.5	28	60	Yes	Yes
30	22	HV22RS	200-230 or 460 3Ph	120.2	109.5	100.2	72	1"	2	1146	32.5	28	60	Yes	Yes
40	30	HV30RS	460 3Ph	188.5	170.5	152.8	73	1.5"	6	2004	43	35	63	Yes	Yes
50	37	HV37RS	460 3Ph	217.8	202.1	183.1	73	1.5"	6	2151	43	35	63	Yes	Yes
60	45	HV45RS	460 3Ph	263.7	243.5	223.7	73	1.5"	6	2187	43	35	63	Yes	Yes

RS Configuration 87-150PSIG