

Quality Package Design

Blazing a new path in reciprocating compressors, the Champion Evolution is a perfect choice for applications with intermittent duty and a low noise requirement. Evolution delivers powerful performance, easy maintenance, and extremely low noise levels all in one package to provide maximum customer satisfaction.

Standard Features

- Dedicated cooling circuits (motor and compressor chambers)
- Oil sight gauge & filter maintenance indicator
- Heavy-duty air cooled aftercooler
- Sound attenuating enclosure
- Magnetic starter for overload protection
- Manual tank drain
- Low oil level shutdown
- Standard start/stop control
- Belt tensioning system & easily removable front and back panels for serviceability
- 1-Year package
- 5-Year pro-rated pump warranty

Available Options

- Moisture separator
- Dual control
- High temperature shut down
- Electric tank drain
- Premium efficiency motors
- Vibration isolators



BARE PUMP

MODEL	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLINDERS	OIL CAPACITY QTS.	MIN/MAX PUMP RPM
RP15B	20.9 × 18.2 × 20.7	109	4.6 & 2.5	3	2	2	400/990

SIMPLEX BASE MOUNTED UNITS

MOTOR HP	EVOLUTION CABQEA	DIMENSIONS L × W × H	APPROX. SHIP WEIGHT	SOUND LEVEL DBA	175 PSI RATING	
ΠP	CADGLA	INCHES	LBS.	UDA	RPM	CFM DEL'Y
5	BER5	41 × 31.5 × 31	505	67	734	16.8
7.5	BER7F	41 × 31.5 × 31	534	68	990	22.4

SIMPLEX HORIZONTAL TANK MOUNTED UNITS

MOTOR	TANK CAPACITY GAL.	EVOLUTION CASQEA	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	SOUND LEVEL DBA	175 PSI RATING	
HP						RPM	CFM DEL'Y
5	80	HER5-8	67 × 31.5 × 53.5	733	67	734	16.8
7.5	80	HER7F-8	67 × 31.5 × 53.5	762	68	990	22.4



1301 North Euclid Avenue Princeton, Illinois 61356 USA www.ChampionPneumatic.com/ContactUs.aspx 866-276-4330 www.ChampionPneumatic.com

> ©2015 Gardner Denver, Inc. Printed in U.S.A. CR-EV-RP15 1st Ed. 11/15



