



COMMANDAIR | 2-3 HP RECIPROCATING COMPRESSORS

Pump Model BWA

The Solution to Your Application

Gardner Denver offers a full line of compact Commandair reciprocating air compressors, which are manufactured to the same quality standards as our larger, industrial models. These packages are sized for smaller air requirements such as small industrial plants, schools, small automotive centers, and do-it-yourselfers.

Standard Features

- Cast iron cylinders
- Lightweight aluminum alloy pistons
- Two compression rings and one oil-control ring
- High density, high silicon die-cast aluminum alloy connecting rods
- High-quality steel reed-type valves
- Precision balanced flywheel
- Rugged ductile iron crankshaft
- Rugged cast-iron crankcase
- Convenient oil level sight gauge
- Removable cartridge-type intake filter
- 1-Year package warranty
- 1-Year pump warranty

Available Options

- Pneumatic or electric tank drain
- Vibration isolators

Gardner
Denver

BARE PUMP

MODEL	DIMENSIONS L x W x H INCHES	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLINDERS	OIL CAPACITY QTS.	MIN/MAX PUMP RPM
BWA	23.4 x 10.2 x 15.8	55	2.6	2	3	.5	500/1000

SIMPLEX BASE MOUNTED UNITS

MOTOR HP	COMPRESSOR PUMP MODEL	COMMANDAIR CESCAA	DIMENSIONS L x W x H INCHES	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLIN- DERS	BOLT DOWN L x W INCHES	90 PSI	
									RPM	CFM DEL'Y
2	BWA	BMBWA20	38.8 x 20.6 x 20.5	102	2.38	2	3	25.6 x 14.5	700	7.2

SIMPLEX VERTICAL TANK MOUNTED UNITS

MOTOR HP	TANK CAPACITY GAL.	COMPRESSOR PUMP MODEL	COMMANDAIR CESCAA	DIMENSIONS L x W x H INCHES	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLIN- DERS	BOLT DOWN L x W INCHES	90 PSI	
										RPM	CFM DEL'Y
3	30	BWA	30BWA30V	32.3 x 22.4 x 51.6	314	2.38	2	3	4 on 18" BC	995	10.2

SIMPLEX HORIZONTAL TANK MOUNTED UNITS

MOTOR HP	TANK CAPACITY GAL.	COMPRESSOR PUMP MODEL	COMMANDAIR CESCAA	DIMENSIONS L x W x H INCHES	APPROX. SHIP WEIGHT LBS.	BORE DIA. INCHES	STROKE INCHES	# OF CYLIN- DERS	BOLT DOWN L x W INCHES	90 PSI	
										RPM	CFM DEL'Y
2	30	BWA	30BWA20H	42 x 21 x 35	212	2.38	2	3	20 x 12.8	700	10.77
2	60	BWA	60BWA20H	51 x 23.5 x 41	303	2.38	2	3	28 x 16.5	700	10.77
3	30	BWA	30BWA30H	42 x 21 x 35	299	2.38	2	3	20 x 12.8	995	15.31

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenver.com/gdproducts



©2018 Gardner Denver, Inc. Printed in U.S.A.
GRCS-CA-BWA 1st Ed. 2/18

Please recycle after use.