## Technical Data

Model		C200TS-24	C220TS-21	C210TS-18	C230TS-17	C240TS-14	C250TS-12	C260TS-10	C270TS-9
Main compressor		Exhaust turbocharged centrifugal primary boosting and screw compressor fulfill secondary compression thanks to imported main compressor.							
Discharge pressure	bar	24	21	18	17	14	12	10	8.6
Displacement	m³/min	20	22	21	23	24	25	26	27

Engine		Engine is imported Cummins QSB6.7 turbocharged engine.				
Displacement of diesel engine	L	6.7				
Emission standard		Euro III				
Rated power of diesel engine	Kw/HP	228(308)				
Rated revolution of diesel engine	rpm	2400				
Rated idling speed of diesel engine	rpm	1000				
Voltage of electrical system	V	24				
Capacity of fuel tank	L	350				
Cooling water temperatur of diesel engine	C	≤107				
Exhaust temperature of compressor	°C	≤117				

## Specifications

Overall dimensions	mm	4530×1900×2525 (with tractor) It is equipped with single shaft and two wheels for speed limit of 20 km/h and with optional skid.				
Chassis system						
Weight	kg	3300	3340			
Interface dimensions		1×G 2" 1×G 3/4"				
Noise	dB	76±3				
Applicable altitude	М	≤5000				
Applicable ambient temperature	°C	-25~52				

In accordance with ISO 1217 Ed.4 2009, Annex D
Based on legal limit value defined in 2000/14/EC directive
Noise level measured at 7 m from machine in accordance with PNEUROP/PN8NTC2.2