

COMPRESSOR DATA SHEET



In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Variable Displacement

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: Gardner Denver		
2	Model Number: SAV-125hp-EAQ-100psi	Date:	06/26/20
	<input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled	Type:	Screw
	<input checked="" type="checkbox"/> Lubricated <input type="checkbox"/> Oil Free	# of Stages:	1
3*	Full Load Operating Pressure ^b	100	psig ^b
4	Drive Motor Nominal Rating	125	hp
5	Drive Motor Nominal Efficiency	95.4	percent
6	Fan Motor Nominal Rating (if applicable)	N/A	hp
7	Fan Motor Nominal Efficiency	N/A	percent
8*	Input Power (kW)	Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	107.9	614	17.57
	100.3	553	18.16
	86.3	430	20.08
	74.7	307	24.32
	71.2	246	29.00
9*	Total Package Input Power at Zero Flow ^{c, d}	21.6	kW
10	Isentropic Efficiency at Full Flow Rated Capacity and Full Load Operating Pressure	75.6	%
11	<p align="center"> <small>Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</small> </p>		

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load Zero Flow Power
m ³ / min	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 032.1