COMPRESSOR DATA SHEET

Gardner Denver

In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors

Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer: Gardner Denver		
	Model Number: STG2-150hp-100psi	Date:	1/4/2021
2	Air-cooled X Water-cooled	Type:	Screw
		# of Stages:	1
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}	783.0	acfm ^{a,e}
4*	Full Load Operating Pressure ^b	100	psig ^b
5	Maximum Full Flow Operating Pressure ^c	100	psig ^c
6	Drive Motor Nominal Rating	150	hp
7	Drive Motor Nominal Efficiency	95.8	percent
8	Fan Motor Nominal Rating (if applicable)	NA	hp
9	Fan Motor Nominal Efficiency	NA	percent
10*	Total Package Input Power at Zero Flow ^e	38.2	kW ^e
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	131.50	$k\mathbf{W}^{d}$
12*	Package Specific Power at Rated Capacity and Full Load Operating Pressure ^e	16.79	kW/100 cfm ^e
13	Isentropic Efficiency	79.14	Percent

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program: <u>www.cagi.org</u>

NOTES:

Compressed Air & Gas Institute

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the
- maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member	m^3 / min	2			No Load / Zero Flow Power
П Г		<u>ft³ / min</u>	%	%	%
	Below 0.5	Below 17.6	+/- 7	+/- 8	
	0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
	1.5 to 15	53 to 529.7	+/- 5	+/- 6	+/- 10%
ROT 030.1	Above 15	Above 529.7	+/- 4	+/- 5	
12/19 Rev 3 This form was developed	by the Compressed Air an	d Gas Institute for the use of its members participating in t	he PVP. CAGI has not indepen	idently verified the reported data	

Configurator: ST125-200G2A