

OPERATING SPECIFICATIONS

MODELS	MIN. OPERATING TEMPERATURE	MAX. OPERATING TEMPERATURE	MAXIMUM PRESSURE	PRESSURE DIFFERENTIAL AT RATED FLOW
7000364	35°F	175°F	200 psig	1.0 psid
7000347-7000356	35°F	175°F	200 psig	1.0 psid

MOISTURE SEPARATORS AND DRAINS

MODEL NUMBER	IN/OUT NPT PIPE CONN.	RATED FLOW (SCFM) @ 100 PSIG ¹	DIMENSIONS (INCHES)						APPROX. WEIGHT (LBS)	RECOMMENDED AUTOMATIC DRAIN	DRAIN DIMENS. (IN.)	OVERALL LENGTH (IN.)	EXTERNAL DRAIN DISCHARGE PORT
			A	B	C	D	E	F					
7000347*	¼"	25	3.00	.90	5.51	3.5	6.41	⅜"	2.2	Optional	—	—	—
7000348	¼"	25	3.00	.90	5.51	3.5	6.41	⅜"	2.2	Internal	—	—	—
7000349*	⅜"	50	3.35	.98	6.36	3.5	7.34	⅜"	2.6	Optional	—	—	—
7000351*	½"	50	3.35	.98	6.36	3.5	7.34	⅜"	2.6	Optional	—	—	—
7000352	½"	50	3.35	.98	6.36	3.5	7.34	⅜"	2.6	Internal	—	—	—
7000353*	¾"	100	4.692	1.0	9.00	3.5	10.0	⅜"	6.0	Optional	—	—	—
7000354	¾"	100	4.62	1.0	9.00	3.5	10.0	⅜"	6.0	Internal	—	—	—
7000355*	1"	120	4.62	1.0	9.00	3.5	10.0	⅜"	6.0	Optional	—	—	—
7000356	1"	120	4.62	1.0	9.00	3.5	10.0	⅜"	6.0	Internal	—	—	—

*Models have petcock

¹psig maximum differential; contact Gardner Denver for flow at higher psigs