

## Technical data

Model	Power		Work Pressure bar	Biggest Pressure bar	F.A.D m <sup>3</sup> /min	Size mm			Weight kg	Connect Size
	HP	kW				L	W	H		
<b>SAV-250</b>	250	187	7.0	7.5	35.9	3150	1829	1880	3884	DN80
			8.0	8.5	30.1					
			10.0	10.5	29.1					
<b>SAV-300</b>	300	224	7.0	7.5	43.3	3150	1829	1880	3931	DN80
			8.0	8.5	37.3					
			10.0	10.5	35.1					
<b>SAV-350</b>	350	262	7.0	7.5	46.0	3150	1829	1880	4875	DN80
			8.0	8.5	43.0					
			10.0	10.5	37.0					
<b>SAV-400</b>	400	298	7.0	7.5	59.5	3750	2180	2050	7600	DN100
			8.0	8.5	54.6					
			10.0	10.5	40.7					
<b>SAV-450</b>	450	335	7.0	7.5	64.1	3750	2180	2050	7800	DN100
			8.0	8.5	61.0					
			10.0	10.5	50.2					
<b>SAV-500</b>	500	372	7.0	7.5	70.8	3750	2180	2050	8000	DN100
			8.0	8.5	65.3					
			10.0	10.5	57.7					
<b>SAV-550</b>	550	410	8.0	8.5	70.6	3750	2180	2050	8200	DN100
			10.0	10.5	64.5					
<b>SAV-600</b>	550	400	7.0	7.5	80.0	3950	2280	2150	8400	DN100
	600	450	* 8.0	8.5	80.0					

