LAND LOADING ARM ACCESSORIES & REPAIR KITS

Emco Wheaton provides a range of Aftermarket accessories for our road and rail loading arms. Our range of premium accessories are designed to maximize the safety and handling of your loading arms and can easily be applied to the arm on site without cutting or welding.

We also provide a wide range of repair kits to service your loading arm on site with ease and minimal downtime.

Our combination of products and services will ensure optimum performance in your bulk liquid transfer operations. Whenever you need assistance, our experienced team can recommend the best accessories and kits for your operation and guide you through on-site integration.

RANGE

Accessories:

- Load valve remote
- Lockdown device
- Spacer spools
- Vacuum breakers
- Position stops
- Grounding straps
- Sight glass
- Grip handle/ bucket hook

Replacement Parts & Repair Kits:

- D2000 seal kits
- Load valve kits
- Aluminum swivel kits
- D2000 module refurbishment
- Hardware & gasket kits (TTMA, 150#, 300#)
- Legacy swivel kits
- API coupler kits
- D2000 modules



www.emcowheaton.com

@EmcoWheaton | If www.facebook.com/EmcoWheaton

©2020 Emco Wheaton. All Rights Reserved. All trademarks are the property of Emco Wheaton.

REQUEST A QUOTE