

3" x 1-1/2" End Suction Centrifugal Pump

Made with high quality investment cast 316 stainless steel components, the ChemFlo® series of pumps are designed to be applied in a wide range of pumping applications where stainless steel is required.

The ChemFlo® 8 pumps utilize an enclosed impeller designed for achieving higher heads and efficiencies than a standard semi-open impeller. Multiple impeller trims allow the ChemFlo® 8 to meet most duty points up to 350 GPM and total head up to 290 feet. Several mechanical seal options are available in addition to the standard type 2100 carbon / ceramic / Viton mechanical seal.

All wetted components are 316 investment cast stainless steel providing superior corrosion resistance when pumping chemical compounds. The Chemflo® 8 pedestal uses a pump end (PumPAK®) design that is interchangeable with 145TC, 184TC, 215TC, 256TC, or 286TSC electric motors. If ordering a PumPAK® with a 145TC please note that the electric motor must have a base.

Application

- Agricultural
- Commercial
- Industrial
- Marine
- OEM

Drive Sleeve

316 stainless steel

SPECIFICATIONS:

Suction And Discharge 3" x 1-1/2" 150# ANSI flange

Materials Of Construction 316 stainless steel
Flow Up to 350 GPM

Head Feet Up to 290'

Impeller 8.0" enclosed, cast 316 stainless steel

Drive Options Close coupled 184TC, Close coupled 215TC, Close coupled 256TC, Close

coupled 286TSC, Close coupled 145TC,


Hydraulic, Pedestal, PumPAK®

Seal Special seal material combinations


available (consult factory), Standard

carbon / ceramic / Viton



























ITEM	PART	DESCRIPTION	MATERIAL	QTY.
1	21255	PIPE PLUG 1/8" NPT	316 SS	2
3	31650	VOLUTE	CF8M SS	1
3	29194	HEX JAM NUT 5/8-18	316 SS	1
4	31648	IMPELLER Ø7.95		1
4	31965	IMPELLER Ø7.75		1
4	31966			1
4	31966	IMPELLER Ø7.00	CF8M SS	1
4	31968	IMPELLER Ø6.50	CF8M SS	1
5	31347			1
5	31374	SEAL ASSEMBLY 1.5"	CCS VITON	1
5	28170	SEAL ASSEMBLY 1.5"	EPDM	1
5	26461		SSC	1
5		SEAL ASSEMBLY 1.5"		1
6	31430	O-RING AS-568-265	VITON	1
6	39262	O-RING AS-568-265	EPDM	1
6	39411			1
7	31426			1
8	37881		NEO RUBBER	1
9	31656			1
10	21260	STUD 3/8-16X1.32		10
11	28053		304 SS	10
12	21268		304 SS	10
13	31802	DRIVE SHAFT	316 SS	1
14		BALL BEARING		2
15	31803		CARBON SPRING	1
16	33232	SQUARE KEY	STEEL	1

CF8 PED