

HV Series

hp	kW	Model	Voltage/Phase	CFM 100 PSIG	CFM 115 PSIG	CFM 150 PSIG	Noise Level (dBA)	Air Outlet NPT	Oil Cap. (Gal)	Weight (lbs.)	L (in.)	W (in.)	H (in.)	Starter	After cooler
15	11	HV11	200-230/460/575 3Ph	-	52.4	45.9	69	.75"	1.85	847	32.5	27.6	60	Yes	Yes
20	15	HV15	200-230/460/575 3Ph	-	67.3	60.6	70	.75"	1.85	875	32.5	27.6	60	Yes	Yes
25	18	HV18	200-230/460/575 3Ph	-	100.4	89.4	71	1"	2	1060	32.5	27.6	60	Yes	Yes
30	22	HV22	200-230/460/575 3Ph	-	112.7	101.3	72	1"	2	1090	32.5	27.6	60	Yes	Yes
40	30	HV30	200-230/460/575 3Ph	-	155.7	143.2	73	1.5"	6	1889	43	35	63	Yes	Yes
50	37	HV37	200-230/460/575 3Ph	-	201.8	175.9	73	1.5"	6	2008	43	35	63	Yes	Yes
60	45	HV45	200-230/460/575 3Ph	-	226.6	198.5	73	1.5"	6	2072	43	35	63	Yes	Yes