

COMPRESSOR DATA SHEET

Federal Uniform Test Method for Certain Air Compressors Not Applicable



Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR

1	Manufacturer:	Gardner Denver		
2	Model Number:	ETS-250hp-100psi	Date:	2/7/2024
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type:	Screw
	<input checked="" type="checkbox"/> Oil-injected	<input type="checkbox"/> Oil-free	# of Stages:	2
3*	Rated Capacity at Full Load Operating Pressure ^{a, e}		1403.7	acfm ^{a,e}
4	Full Load Operating Pressure ^b		100	psig ^b
5	Maximum Full Flow Operating Pressure ^c		107	psig ^c
6	Drive Motor Nominal Rating		250	hp
7	Drive Motor Nominal Efficiency		96.2	percent
8	Fan Motor Nominal Rating (if applicable)		N/A	hp
9	Fan Motor Nominal Efficiency		N/A	percent
10*	Total Package Input Power at Zero Flow ^e		68.40	kW ^e
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d		217.57	kW ^d
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure ^e		15.50	kW/100 cfm ^e

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program: www.cagi.org

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.



Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
<u>m³ / min</u>	<u>ft³ / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 030.2