

**COMPRESSOR DATA SHEET**



**Federal Uniform Test Method for Certain Air Compressors Not Applicable**

**Rotary Compressor: Fixed Speed**

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer:	<b>Gardner Denver</b>	
2	Model Number:	<b>L290-340hp-100psi</b>	Date: <b>1/4/2021</b>
	<input checked="" type="checkbox"/> Air-cooled <input type="checkbox"/> Water-cooled		Type: <b>Screw</b>
	<input checked="" type="checkbox"/> Oil-injected <input type="checkbox"/> Oil-free		# of Stages: <b>1</b>
3*	Rated Capacity at Full Load Operating Pressure <sup>a, e</sup>	<b>1617.7</b>	acfm <sup>a,e</sup>
4	Full Load Operating Pressure <sup>b</sup>	<b>100</b>	psig <sup>b</sup>
5	Maximum Full Flow Operating Pressure <sup>c</sup>	<b>110</b>	psig <sup>c</sup>
6	Drive Motor Nominal Rating	<b>340</b>	hp
7	Drive Motor Nominal Efficiency	<b>95.8</b>	percent
8	Fan Motor Nominal Rating (if applicable)	<b>3.0 / 10.1</b>	hp
9	Fan Motor Nominal Efficiency	<b>86.7 / 90.4</b>	percent
10*	Total Package Input Power at Zero Flow <sup>e</sup>	<b>87.6</b>	kW <sup>e</sup>
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>d</sup>	<b>294.84</b>	kW <sup>d</sup>
12*	Specific Package Input Power at Rated Capacity and Full Load Operating Pressure <sup>e</sup>	<b>18.23</b>	kW/100 cfm <sup>e</sup>

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)

- NOTES:
- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
  - b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
  - c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
  - d. Total package input power at other than reported operating points will vary with control strategy.
  - e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
<u>m<sup>3</sup> / min</u>	<u>ft<sup>3</sup> / min</u>	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	+/- 10%
Above 15	Above 529.7	+/- 4	+/- 5	



Member

ROT 030.2