## 2505 Series



## **FEATURES**

- > Oil-less operation
- > Permanently lubricated bearings
- > Stainless steel valves
- > Die-cast aluminum components
- > Dynamically balanced
- > Proven WOB-L technology
- > Monolithic head
- > Field service capability
- > Thermally protected motor
- > Designed and tested per Agency standards
- > RoHS compliant

Declaration documentation available upon request

## TYPICAL APPLICATIONS

- >O2 Concentrator
- > Blood & Laboratory Analyzers
- > Dental & Optical Equipment
- > Medical Trauma Carts
- > Laboratory Air Dryers
- > Aspirators/Respirators
- > Industrial/Manufacturing Equipment

# BASE MODELS

2505CE38 (115/60/1) 2505CG38 (230/60/1) 2505CHI45 (220-240/50/1)






### 2505 Series

Flow	3.4 cfm (96.3 l/min)	
Max. pressure	100 psi (6.9 bar)	
Max. vacuum	90% local barometer	







NOTE: All test values are nominal and for reference only. They are not guaranteed maximum or minimum limits, nor do they imply mean or median values.


PERFORMANCE DATA	T15-0120	T14-0320	T14-0320
Model Number	2505CE38	2505CG38	2505CHI45
Head Configuration	Pressure/vacuum parallel flow	Pressure/vacuum parallel flow	Pressure/vacuum parallel flow
Stroke	0.38 in. (9.6 mm)	0.38 in. (9.6 mm)	0.45 in. (11.4 mm)
Nominal voltage input	115/60/1	230/60/1	220-240/50/1
Max. open air flow	3.4 cfm (96.3 l/min)	3.4 cfm (96.3 l/min)	3.4 cfm (96.3 l/min)
Max. rated pressure	100 psi (6.9 bar)	60 psi (4.1 bar)	35 psi (2.4 bar)
Current at rated pressure	3.6A	1.9A	1.7A
Power at rated pressure	380W	415W	385W
Speed at rated pressure	1700 rpm	1670 rpm	1400 rpm
Max. pressure restart	Consult factory	Consult factory	Consult factory
Max. vacuum	90% local barometer	90% local barometer	90% local barometer
Max. vacuum restart	Consult factory	Consult factory	Consult factory

ELECTRICAL DATA					
Motor type (Capacitance)	P.S.C. [22 µF]	P.S.C. [12.5 μF]	P.S.C. [12.5 μF]		
Motor locked rotor current	11.8A	4.0A	4.5A		
Motor insulation class	В	В	В		
Thermal switch (Nominal Open temperature)	Yes [275°F (135°C)	Yes [275°F (135°C)]	Yes [275°F (135°C)]		
Lead wire color, gauge	Brown(hot), blue(neutral), 18 AWG	Brown(hot), blue(neutral), 18 AWG	Brown(hot), blue(neutral), 18 AWG		
Capacitor lead wire color, gauge	Black, black, 18 AWG	Red, red, 18 AWG	Red, red, 18 AWG		

GENERAL DATA					
Operating ambient temperature	50° to 104°F (10°C TO 40°C)*	50° to 104°F (10°C TO 40°C)*	50° to 104°F (10°C TO 40°C)*		
Safety Certification	cRUus	TUV	TUV		
Net weight	14.0 lbs (6.4 kg)	14.0 lbs (6.4 kg)	14.0 lbs (6.4 kg)		

<sup>\*</sup>Broader ambient operating ranges may be possible depending on your specific application. Please consult factory regarding your particular system needs.

#### PRODUCT DIMENSIONS



### PUMP AND COMPRESSOR SOLUTIONS FOR OEMS WORLDWIDE







Gardner Denver Thomas GmbH

Livry-Gargan-Str. 10 82256 Fürstenfeldbruck Germany T +49 8141 2280 0

F +49 8141 8892136

Gardner Denver Thomas Pneumatic Systems (Wuxi) Co. Ltd.

1 New Dongʻan Road, Suofang Town Xinwu District, Wuxi Jiangsu, 214142 P.R. China T +86 510 6878 2217 F +86 510 6878 2200

 $thomas. de@gardnerdenver.com \\ thomas. cn@gardnerdenver.com$ 

Gardner Denver Thomas, Inc.

1419 Illinois Avenue Sheboygan, WI 53081 USA

T +1 920 4574891 F +1 920 4514276

td. us a@gardner denver.com

The information presented in this material is based on technical data and test results of nominal units. It is believed to be accurate and reliable and is offered as an aid to help in the selection of Thomas products. It is the responsibility of the user to determine the suitability of the product for the intended use and the user assumes all risk and liability in connection there with. Thomas does not warrant, guarantee or assume any obligation or liability in connection with this information.

Models presented in this catalog are representative of the product family. Photos of products pictured in this catalog do not necessarily represent a specific model number. To obtain further information for custom options, contact your local Thomas office.

Printed in U.S.A Form No. 850-4019 04/2018 © Gardner Denver Thomas, Inc. All rights reserved.