

**COMPRESSOR DATA SHEET**



**In Accordance With Federal Uniform Test Method for Certain Lubricated Air Compressors**

**Rotary Compressor: Variable Frequency Drive**

MODEL DATA - FOR COMPRESSED AIR				
1	Manufacturer: <b>Gardner Denver</b>			
2	Model Number: <b>L132RS(F)-190#</b>		Date:	<b>12/17/21</b>
	<input checked="" type="checkbox"/> Air-cooled	<input type="checkbox"/> Water-cooled	Type:	<b>Screw</b>
				# of Stages: <b>1</b>
3*	Full Load Operating Pressure <sup>b</sup>		<b>125</b>	psig <sup>b</sup>
4	Drive Motor Nominal Rating		<b>180</b>	hp
5	Drive Motor Nominal Efficiency		<b>96.0</b>	percent
6	Fan Motor Nominal Rating (if applicable)		<b>8.8</b>	hp
7	Fan Motor Nominal Efficiency		<b>91.0</b>	percent
8*	Input Power (kW)		Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	158.44		<b>791.0</b>	<b>20.03</b>
	131.11		<b>678.9</b>	<b>19.31</b>
	108.78		<b>563.9</b>	<b>19.29</b>
	86.31		<b>445.5</b>	<b>19.38</b>
	64.75		<b>321.3</b>	<b>20.16</b>
	42.47		<b>179.0</b>	<b>23.72</b>
9*	Total Package Input Power at Zero Flow <sup>c, d</sup>		<b>14.6</b>	<b>kW</b>
10	Isentropic Efficiency		<b>76.43</b>	<b>%</b>
11	<p align="center"><b>Note: Graph is only a visual representation of the data in Section 8</b>                      Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35                      X-Axis Scale, 0 to 25% over maximum capacity</p>			

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator  
 Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:  
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	Zero Flow Power
m <sup>3</sup> / min	ft <sup>3</sup> / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.1