

CHEMFLO® 8 HYDRAULIC 3" x 1-1/2" End Suction Centrifugal Pump

Made with high quality investment cast 316 stainless steel components, the ChemFlo® series of pumps are designed to be applied in a wide range of pumping applications where stainless steel is required.

The ChemFlo® 8 hydraulic pumps utilize an enclosed impeller designed for achieving higher heads and efficiencies than a standard semi-open impeller. Multiple hydraulic flows allow the ChemFlo® 8 to meet most duty points up to 395 GPM and total head up to 305 feet. Several mechanical seal options are available in addition to the standard type 2100 carbon / ceramic / Viton mechanical seal.

ChemFlo® 8 hydraulic pumps are offered with a 1.59 cubic inch displacement SAE port fitting gerotor type motor for hydraulic flows up to 26 GPM and a maximum pressure of 2400 PSI. Some hydraulic motors are bi-rotational.



Application


- Agricultural
- Commercial
- Industrial
 Marine
- OEM

SPE	CIFIC	CATI	ON	S:

Suction And Discharge	3" x 1-1/2" 125# ANSI flange
Materials Of Construction	316 stainless steel, Stainless steel
Flow	Up to 395 GPM
Head Feet	Up to 305'
Impeller	8.0" enclosed, cast 316 stainless steel
Drive Options	Hydraulic motor 1.59 cu. in.
Seal	Special seal material combinations available (consult factory), Standard carbon / ceramic / Viton
Psi	Up to 134
Hydraulic Motor	Gerotor
Hydraulic System Pressure	Up to 2400 PSI
Hydraulic Fluid Flow	Up to 26 GPM




CHEMFLO® 8 HYDRAULIC





34800 BENNETT - FRASER, MI 48026-1686 (586) 293-8240 - FAX (586) 293-8469 (800) 563-8006 - www.mppumps.com

CHEMFLO® 8 HYDRAULIC





		5 6			
	ITEM NO.	PART NUMBER		MATERIAL	QTY.
	1	31520	CAPSCREW 3/8-16X1.0 LG		10
	2	31312	CLAMP	STEEL	1
	3 4	26680 26998	SLINGER SNAP RING	NEOPRENE RUBBER STEEL	2
	5	26990	BALL BEARING	STEEL	2
	6	33367	SHAFT	316 SS	1
(13) (14) (15) (16) (17) (18) (19) (20) (21) (22)	7	26994	BODY	CAST IRON	i
	8	21266	LOCKWASHER 3/8 X 1/8	304 SS	8
	9	41259	CAPSCREW 3/8-16X1.75	STEEL	8
	10	29993	HYDRAULIC MOTOR	CAST IRON	1
	11	21254	LOCKWASHER 1/2"	304 SS	2 2
	12	21246	CAPSCREW 1/2-13X1.25	304 SS	2
	13	21255	PIPE PLUG 1/8" NPT	316 SS	2
	14	31650	VOLUTE	CF8M SS	1
	15 16	29194 31648	HEX JAM NUT 5/8-18 IMPELLER Ø7.95	316 SS CF8M SS	1
	16	31648	IMPELLER Ø7.95	CF8M SS	1
	16	31966	IMPELLER Ø7.50	CF8M SS	1
	16	31966	IMPELLER Ø7.00	CF8M SS	1
	16	31968	IMPELLER Ø6.50	CF8M SS	1
	17	31311	DRIVE SLEEVE	316 SS	1
	18	31372	SHIM	316 SS	1
	19	31347	SEAL ASSEMBLY 1.5"	STC/316 SS	1
	19	31374	SEAL ASSEMBLY 1.5"	CCS VITON	1
	19	28170	SEAL ASSEMBLY 1.5"	EPDM	
	19	26461	SEAL ASSEMBLY 1.5"	SSC	1
	20	26565 31430	SEAL ASSEMBLY 1.5" O-RING AS-568-265	CHEMLON	1
	20	39262	O-RING AS-568-265	EPDM	1
	20	39411	O-RING AS-568-265	BUNA	i
	21	31426	SEAL HOUSING	CF8M SS	1
CHEMFLO 8 W/1.59 DISP. HYDRAULIC MOTOR					