COMPRESSOR DATA SHEET



Federal Uniform Test Method for Certain Air Compressors Not Applicable

Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR									
1	1 Manufacturer: Gardner Denver								
2	Model Number: VST225-150hp(2S)-100psi			Date:	01/04/21				
	Air-cooled X	Air-cooled X Water-cooled		Type:	Screw				
	X Lubricated Oil Free		# of Stages:	2					
3*	Full Load Operating Pressur	Full Load Operating Pressure b		psig b					
4	Drive Motor Nominal Rating		2 x 150	hp					
5	Drive Motor Nominal Efficiency		94.0	percent					
6	Fan Motor Nominal Rating (if applicable)		NA	hp					
7	Fan Motor Nominal Efficien	an Motor Nominal Efficiency		percent					
	Input Power (kW)		Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d					
	271.36		1728.0	15.70					
0.4	228.50		1468.8	15.56					
8*	186.18		1209.6	15.39					
	146.03		950.4	15.37					
	108.65		691.2	15.72					
	70.10	c, d	406.0	17.27					
9*	Total Package Input Power a	0.0	kW						
10	35.00 30.00 15.00 10.00 20.00 400.0 600.0 800.0 1000.0 1200.0 1400.0 1600.0 1800.0 2000.0 Capacity (ACFM) Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity								

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$\underline{\mathbf{m}}^3 / \underline{\mathbf{min}}$	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2

12/19 R3

This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: VST225-260B