

# NASH ECO-FLO® UPGRADE

REDUCE WATER USAGE AND COST BY UP TO 50%

The NASH ECO-FLO upgrade reduces the seal water flow up to 50% than the original requirement, effectively cutting water usage in half and lowering operating costs without impacting pump performance or reliability.

In addition to increased efficiency, the ECO-FLO upgrade improves the operating stability of the pump, particularly in operations where there are rapid changes to the operating vacuum level. The upgrade eliminates over-compression, improves handling of system upsets and reduces stress on the drive system.

This patented upgrade is available on new and existing NASH CL and 2BE3/4 pumps without changes to the inlet and discharge piping, allowing upgraded pumps to fit existing system designs.


Reduce water consumption and cost, improve operating efficiency. ECO-FLO, only from Gardner Denver Nash.

- Reduce water consumption & cost by up to 50%
- 12 month or less payback
- Same performance and reliability
- Improves handling of system upsets
- Bolt in replacement - inlet and discharge piping unchanged, uses existing base & motor

## ESTIMATED WATER COST SAVINGS

MODEL	SEAL WATER RATE (GPM)		ANNUAL WATER SAVINGS (GALLONS)	ESTIMATED ANNUAL COST SAVINGS	
	EXISTING	WITH ECO-FLO			
CL	2002	40	20	10 MILLION	\$ 15,700
	3002	70	35	18 MILLION	\$ 27,600
	4002	50	25	13 MILLION	\$ 19,700
	6002	80	40	21 MILLION	\$ 31,500
	9002	120	60	32 MILLION	\$ 35,400
2BE3/4	30	24	12	6 MILLION	\$ 9,460
	72	184	92	48 MILLION	\$ 72,532

Estimated savings based on \$1.50/1,000 gal H<sub>2</sub>O, 8,750 operating hours/year Once thru operation



# ECO-FLO

## NASH ECO-FLO®

Patented upgrade, available exclusively from Gardner Denver Nash and NASH CERTIFIED™ Service Centers.

“We started the pump up on December 27th and she’s been running beautifully since. You can barely hear it running and there was quite a significant reduction in seal water consumption.”

Bryan Patterson  
PM Services AbitibiBowater - Fort Frances  
(comment about ECO-FLO upgrade)

- Reduces water usage by up to 50%
- Improves handling of system upsets
- Inlet & discharge piping unchanged - bolt in replacement
- Uses existing base, motor and drive
- Potential payback of less than 6 months
- Available in both cast iron and stainless steel
- NASH CERTIFIED 2 Year Warranty
- Patented Upgrade - Overhaul to exact Nash standards at a NASH CERTIFIED™ Service Center



Only NASH Certified Service centers are authorized to offer OEM parts, have a complete library of original drawings, and a team of factory trained technicians who can repair and restore your equipment to OEM specifications. With patented upgrades, and 24/7 global service, NASH Certified Service centers are able to provide fast, reliable, and safe service and repair, at a competitive price.

Only NASH Certified™ Service provides the quality, reliability and performance of your original NASH Pump. Guaranteed. **Need repairs done right the first time? You need NASH.**

**Gardner  
Denver**

**NASH**

**Gardner Denver Nash, LLC**

PO Box 130  
Bentleyville, PA 15314 USA  
800-553-NASH  
+1 724 239 1500

[nash@gardnerdenver.com](mailto:nash@gardnerdenver.com)  
[www.GDNash.com](http://www.GDNash.com)

©2017 Gardner Denver Nash, LLC Printed in U.S.A.  
APP-ECO-FLO-1076 3RD EDITION 08/2017  
SUPERSEDES 1076C & 1109A

 Please recycle after use.