

POSITIVE DISPLACEMENT BLOWER

Conveying Solutions



the BLEND

Your systems are not all the same—why should your blower be?





DUROFLOW

Solid Bi-Lobe

Heavy Duty Large Air



RBS SERIES

Tri-Lobe

Heavy Duty Large Air

GOOD

BET

Gardner Denver has more blower technology styles than anyone else.

We can help you customize your system to meet your needs. More technology styles provides tailored options for you.



HELIFLOW

Twisted Tri-Lobe

Low Noise Heavy Duty Large Air



CYCLOBLOWER

Screw

Energy Savings Low Noise Heavy Duty Large Air



CYCLOBLOWER H.E.

Screw

Most Efficient High Pressure Low Noise Heavy Duty Large Air

TER

BEST

the NETWORK






We're Where You Need Us


the SIZING

QuickPik helps you customize our products to meet your demands.

Try it now! Scan the QR code or visit:

www.GDQuickPik.com






Sizing Made Simple

- Accessible information at your fingertips
- Compare & contrast blowers
- Fit technology to your exact needs
- Mobile-friendly design for your laptop, tablet & phone
- Will work off-line
- Set up and customize your profile
- Save selections for future reference



SAVING MONEY




Save Money

CYCLOBLOWER H.E. VS. STRAIGHT LOBE

		@ 15 PSI	PER YEAR
S	standard Straight Lobe	163	\$106,695
	CycloBlower H.E.	129	\$84,604
operation) a	ssuming motor drive efficiency of 90% and ele	etricity cost of \$0.097kWii.	\$22,090 ANNUAL SAVINGS

HIGH PRESSURE



Innovation Working for You!

- In many comparable applications, the CycloBlower operates more efficiently
- CycloBlower H.E. delivers higher pressure than other straightlobe blowers
- Lower Horsepower = Lower Operating Costs
- Higher Pressure = New Conveying Possibilities



The CycloBlower H.E.

- Can support dense phase conveying
- Oil-free compressed air
- Eliminates the need for traditional air compressors
- Best-in-class energy efficiency

the LEGACY

The ORIGINAL Rotary Screw Blower

A Reputation Earned by a Proven History of Quality, Reliability, and Performance

CycloBlower: Unique Screw Design

- Decades of proven results
- Efficient, shock-free compression
- Dependable quality
- High capacity
- Energy savings made possible by screw design
- Ideal for continuous operation

- Can be used for dense phase applications
- Clean air/gas delivery
- Installation flexibility
- Low cost installation






Experience Matters: Over 25,000 CycloBlower Installations World-Wide



Protect your ears,
Protect your WORKFORCE



The HeliFlow Series

REDUCED PULSE = LOWER NOISE = QUIETER OPERATION

Lower Noise

Discharge pulsation is the chief contributor to high noise levels. HeliFlow provides the lowest pressure pulse in the lobe blower market. This reduces noise levels by 4-7 dBA over similar sized, straight-lobe blowers.

Reduced Pulsations

HeliFlow provides more consistent flow variation, reducing the potential for damage to downstream valves and instrumentation.

2 YEAR WARRANTY

From date of initial use or 30 months from date of shipment

Higher Reliability

Discharge pressure pulsation causes axial thrust and higher variations in torque resulting in reduced bearing life. The HeliFlow smooth pulse operation extends the life of the blower.



the TRI-LOBE


Available in 29 Sizes

The RBS Series Delivers


- Solid Tri-Lobe Rotors Offer Quiet, Efficient Operation
- Robust Design for Reliability
- Flexible Mounting Options for Easy Drop-in Replacement
- Dual Splash Lubrication
- 100,000 Hour Bearing Life
- Increased Efficiencies

Options


- Stainless Steel Options
- High Vacuum Options
- Force Feed Lubrication
- Pre-Package Availability
- Special Seal Options




Single Mechanical Seal




Lip Seal



Double Mechanical Seal



Gland Seal



Design Advantages

Dual Splash Lubrication

Reliable dual splash lubrication on both the drive and gear ends for longer product life.

Helical Gears


Helical timing gears for smooth and quiet operation at all speeds.

Leak Free Operation

Piston rings and flinger maximize seal life in continuous severe duty applications.

Durable Shafts

High strength shafts that allow higher operating pressures and rotation speeds.



Long Life Bearings

Reinforced roller bearings are calculated for a lifespan of 100,000 hours under the most severe operating conditions.

Three-Lobe Rotors

Involute Three-Lobe Rotors offer the highest performances and efficiencies.

Single Piece Cylinder

High strength impeller case is heavily ribbed and machined from a single piece of cast iron to retain internal clearances and improve heat dissipation.



TOUGHNESS

Designed for Dusty, Abrasive Environments

- Single piece, high-strength rotor casting
- Oversized bearings
- Dual-splash lubrication
- Advanced oil and air seals
- ISO 9001 quality certified



Built for YOU, Built to LAST















Our blowers are designed to run cooler & protect your product



Sutorbilt

- Coolest in its class
- The most versatile blower available
- Over 240 configuration options
- Grease- or dual-splash lubrication
- Quiet series option

For over 75 years, the Sutorbilt family of positive displacement blowers and vacuum pumps have been synonymous with quality and reliability. The Sutorbilt line is at the heart of an ever-expanding variety of air solutions working every minute of every day around the globe.







the Complete Package

Gardner Denver has more blower package options than anyone else

We can help you customize your system to meet your needs. More technology designs provides tailored options for you.

- Smart Design
- Easy Maintenance
- Compact Installation
- Quiet Operation
- Enclosed or Unenclosed Available
- Inverter Duty Motors for VFD Capabilities

IQ-RB

SIMPLE

Straight Tri-Lobe

Pressure to 15 PSI

Vacuum to 15 inHg


5,500 Max CFM

3-500 HP


Fixed Speed


Mechanical Gauges





the RANGE





The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-428-4890 www.gardnerdenver.com/gdproducts





©2017 Gardner Denver, Inc. Printed in U.S.A. PD-APP-CONVEY 3rd Ed. 4/17

