

ELECTRA SAVER II G2 40-200 HP ROTARY SCREW COMPRESSOR, 60 HZ

MODEL	DRIVE MOTOR		NOMINAL PRESSURE		FAD		NOISE LEVEL*	WEIGHT		DIMENSIONS L x W x H IN. (MM)
	HP	KW	PSIG	BAR	ACFM	M ³ /MIN	DB(A)	LBS	KG	
STG2-40	40	30	100	6.9	204	5.78	78	2098	952	
			125	8.6	192	5.44				
			150	10.3	162	4.59				
			175	12.0	148	4.19				
			200	13.8	137	3.88				
STG2-50	50	37	100	6.9	251	7.11	78	2164	982	
			125	8.6	233	6.60				
			150	10.3	213	6.03				
			175	12.0	191	5.41				
			200	13.8	170	4.81				
STG2-60	60	45	100	6.9	305	8.64	79	2404	1090	
			125	8.6	287	8.14				
			150	10.3	249	7.05				
			175	12.0	219	6.20				
			200	13.8	217	6.14				
STG2-75	75	55	100	6.9	411	11.64	81	4521	2051	
			125	8.6	365	10.34				
			150	10.3	305	8.64				
			175	12.0	263	7.45				
			200	13.8	261	7.39				
STG2-100	100	75	100	6.9	541	15.32	81	4660	2114	
			125	8.6	496	14.05				
			150	10.3	434	12.29				
			175	12.0	346	9.80				
			200	13.8	345	9.77				
STG2-125	125	90	100	6.9	684	19.37	88	7800	3538	
			125	8.6	630	17.84				
			150	10.3	560	15.86				
			175	12.0	475	13.45				
			200	13.8	472	13.37				
STG2-150	150	110	100	6.9	783	22.17	88	8000	3629	
			125	8.6	730	20.67				
			150	10.3	662	18.75				
			175	12.0	553	15.66				
			200	13.8	552	15.63				
STG2-200	200	160	100	6.9	1091	30.89	88	9950	4513	
			125	8.6	986	27.92				
			150	10.3	861	24.38				
			175	12.0	732	20.73				
			200	13.8	724	20.50				

*Noise level, weights and dimensions are for unenclosed models.