

COMPRESSOR DATA SHEET
Federal Uniform Test Method for Certain Air Compressors Not Applicable
Rotary Compressor: Variable Frequency Drive

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer: Gardner Denver		
2	Model Number	TVS55	Date: 07/12/21
	<input type="checkbox"/> Air-cooled <input checked="" type="checkbox"/> Water-cooled		Type: Screw
	<input type="checkbox"/> Lubricated <input checked="" type="checkbox"/> Oil-Free		# of Stages: 2
3*	Full Load Operating Pressure ^b	150	psig ^b
4	Drive Motor Nominal Rating	75	hp
5	Drive Motor Nominal Efficiency	95.2	percent
6	Fan Motor Nominal Rating (if applicable)	0.5	hp
7	Fan Motor Nominal Efficiency	70.0	percent
8*	Input Power (kW)	Capacity (acfm) ^{a,d}	Specific Power (kW/100 acfm) ^d
	67.2	269	24.97
	66.4	263	25.20
	65.6	258	25.45
	64.8	252	25.72
	64.1	246	26.00
9*	Total Package Input Power at Zero Flow ^{c,d}	0.0	kW
	<div style="text-align: center;"> <p>Note: Graph is only a visual representation of the data in Section 8 Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity</p> </div>		
10			

*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator. Consult CAGI website for a list of participants in the third party verification program: www.cagi.org



Member

- Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- Tolerance is specified in ISO 1217, Annex E, as shown in table below:
NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m^3/min	ft^3/min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 031.2