

# ELECTRA SAVER 350-500 HP ROTARY SCREW COMPRESSOR

MODEL	DRIVE MOTOR		50 Hz				60 Hz							
			NOMINAL PRESSURE		FAD		NOMINAL PRESSURE		FAD		NOISE LEVEL <sup>1</sup>	WEIGHT		DIMENSIONS L x W x H IN. (MM)
			PSIG	BAR	ACFM	M <sup>3</sup> /MIN	PSIG	BAR	ACFM	M <sup>3</sup> /MIN	DB(A)	LBS	KG	
SAV-350	350	260	100	6.9	1800	50.99	100	6.9	1684	47.71	84	14200	6441	
			125	8.6	1390	39.38	125	8.6	1434	40.62				
			150	10.3	1120	31.73	150	10.3	1166	33.03				
SAV-400	400	298	100	6.9	2070	56.64	100	6.9	1943	55.04	84	14500	6577	153 x 84 x 78 (3886 x 2134 x 1981)
			125	8.6	1670	47.31	125	8.6	1652	46.80				
			150	10.3	1310	37.11	150	10.3	1414	40.06				
SAV-500	500	373	100	6.9	2580	73.09	100	6.9	2459	69.66	85	15000	6804	
			125	8.6	2050	58.07	125	8.6	2118	60.00				
			150	10.3	1700	48.16	150	10.3	1634	46.29				

\* 110 psig available as field set option only. Order 100 psig unit and reset operating pressure in the field.

1) Noise level, weights and dimensions are for unenclosed models.