

FLOMAX 10 HYDRAULIC

2" x 2" Self Priming Centrifugal Pump

FLOMAX® 10 Hydraulic self-priming centrifugal pumps are capable of creating vacuum sufficient to lift liquids from heights up to 25 feet above the source. Once primed, the pump's built in flapper valve will maintain a full column of liquid in the suction line.

A FLOMAX® 10 hydraulic pump is available with a .73 cubic inch displacement gear motor with hydraulic flows ranging from 8 GPM to 15 GPM and hydraulic pressures ranging from 500 PSI to 1700 PSI.

Standard features include stainless steel drive sleeve, stainless steel fasteners, renewable wear plate, and a semi-open dynamically balanced impeller. Options include double grease lubricated seals, stainless steel impeller and seals for all types of abrasive and/or corrosive services.

The FLOMAX® series of pumps are commonly used in Industrial, Agricultural and Marine applications, such as: Bilge Pumps, Auxiliary Fire Pumps, Ballast Transfer Pumps, Washdown Pumps, Fertilizer and Pesticide Pumps, Applicators & Sprayers, Blending Pumps, Nurse Tanks, Bulk Transfer Pumps and much more.

SPECIFICATIONS:

Suction And Discharge 2" x 2" NPT ports

Materials Of Construction Bronze, Cast iron

Flow Up to 200 GPM

Head Feet Up to 195'
Impeller 6.0" semi-open

Drive Options Hydraulic motor .73 cu. in.

Seal Special seal material combinations

available (consult factory), Standard

carbon / ceramic / Viton

Psi Up to 85

Max Solid Size .625" diameter
Hydraulic Fluid Flow Up to 15 GPM

Options Hydraulic motors with flow control

Hydraulic System Pressure Up to 1700 psi

Hydraulic Motor Gear


Application

- Agricultural
- Industrial
- Marine
- OEM

Features


- Renewable wear plate
- Stainless steel drive sleeve
- · Stainless steel fasteners
- Up to a 25' suction lift

FLOMAX 10 HYDRAULIC






FLOMAX 10 HYDRAULIC





28552



	ITEM NO.	PART NO.	DESCRIPTION	QTY.		ITEM NO.	PART NO.	DESCRIPTION	QTY.
•	1	41481	PIPE PLUG C.I 3/4" NPT	2	*	13	22361	SEAL ASSY 1.5 TYPE 21 - VITON	1
	2	22351	HOUSING C.I.	1	*	14	29715	O RING - VITON	1
*	3	23040	FLAPPER ASSY. BUNA	1		AA	22348	ADAPTER C.I.	1
	4	21291	CAPSCREW S.S 3/8-16 X 1.13	8		16	21260	STUD 3/8-16 X 1.32 S.S.	6
	5	21266	LOCKWASHER S.S 3/8	8		17	21268	HEXNUT S.S 3/8-16	6
	6	22369	SUCTION FLANGE - C.I.	1		18	22460	LIFTEYE ZPS 5/8-11 X 10"	1
*	7	37138	O RING	1		19	22461	HEXNUT S.S 5/8-11	1
	8	22372	DISCHARGE FLANGE - C.I.	1		20	22356	CLAMP S.S 1"	2
*	9	22244	WEAR PLATE STEEL	1		21	21269	CAPSCREW S.S 3/8-16 X 2.25	2
	10	37115	FLAT HD SCREW S.S 3/8-16	2		22	21259	HEX HEAD S.S 3/8-16	4
	11	24721	IMPELLER DUCTILE - 5.75 DIA.	1		23	28551	PEDESTAL ASSY ULTRA	1
*	12	22240	GASKET .032 - NI-2085	1					

*RECOMMENDED REPLACEMENT PARTS

