

SERIES 60 1-1/4" x 1" End Suction Centrifugal Pump

SERIES 60 end suction centrifugal pumps are close-coupled to standard NEMA "C" face motors. Series 60 models are available in cast iron construction to suit a wide variety of liquids. Bronze impellers are available.

All fasteners are stainless steel to reduce corrosion. Impellers are dynamically balanced to improve efficiency and bearing life.

Standard carbon / ceramic / Viton mechanical seal is self-adjusting and corrosion resistant to handle almost any liquid.

Completely tested "Wet End" PumPAKs are available without motors. The MP PumPAK® can be mounted to standard NEMA C frame motors in just minutes.




Application


- Agricultural
- Commercial
- IndustrialOEM
- OEIVI

SPECIFICATIONS:

Suction And Discharge	1-1/4" x 1" NPT
Materials Of Construction	Cast iron
Flow	Up to 65 GPM
Head Feet	Up to 112'
Impeller	5.5" enclosed, cast iron or bronze
Motor	Up to 3 HP
Drive Options	Close coupled 56C, Hydraulic motor .37 cu. in., Hydraulic motor .45 cu. in., Hydraulic motor .58 cu. in., PumPAK® (without motor)
Seal	Special seal material combinations available (consult factory), Standard carbon / ceramic / Viton
Max Solid Size	.11"









SERIES 60 5.50 Impeller



SERIES 60







CLOSE COUPLED FOR ELECTRIC MOTOR DRIVE

SERIES 60 STRAIGHT CENTRIFUGAL PUMPAKS

with Mechanical Seal 1¼" x 1" Pipe Size




PHOTO IS TYPICAL VIEW ONLY

IMPORTANT: When ordering parts, specify model and serial number shown on nameplate.

			QUANTITY REQUIRED PER MODEL		
			ROTATION	Right Hand	
ITEM NO.	PART NO.	DESCRIPTION	PIPE SIZE	1 Va"x1"	
			METAL	Cast Iron	
			MODEL NUMBER	27667	
				27670	
				27673	
				27727	
IOUSING	3				
	27730	Housing Assembly—Includes:		1	
3 6	27658	Housing — Cast Iron		1	
6	21255	Pipe Plug — S.S. — 1/6" NPT		2	
1	1 27665 Gasket			ī	
4	24965	Capscrew - S.S %is"		4	
MPELLE	R				
10	27662	Impeller — Bronze 5.50" dia. for Model 27667		1	
10	27663	Impeller — Bronze 5.00" dia. for Model 27670		1	
10	27664	Impeller - Bronze 4.50" dia, for Model 27673		1	
10	27731	Impeller - Bronze 4.10" dia. for Model 27727		1	
15	22131	Impeller Drive Sleeve %"		1	
9	22588	Lock Nut S.S %"		1	
2 21865 Impeller Drive Key					



SERVICE PARTS LIST Form 7088B



SERIES 60

			QUANTITY REQUIRED PER MODEL		
			ROTATION	Right Hand	
ITEM NO.	PART		PIPE SIZE	1%"x1"	
	NO.	DESCRIPTION	METAL	Cast Iron	
			MODEL NUMBER	27667	
				27670	
				27673	
				27727	
CLAMP					
8	23002	Clamp Assembly — Includes:		1	
		Clamp		2	
5	21284	Hex Nut — S.S. — Yes"		2	
18 16	21238	Lockwasher — S.S. — We'	2		
16	21264	Capscrew — S.S. — We	2		
SEAL					
7	22272	Seal Assembly		1	
11	22133	Seal Spring Retainer	1		
ADAPTO	R				
14	28593	Adaptor — Cast Iron		1	
12	21251	Capscrew - S.S %"		4	
13	21266	Lockwasher - S.S %"		4	




Form 7088B



SERIES 60

27667



	ITEM NO.	PART NO.	DESCRIPTION	QTY.
	1	27658	HOUSING C - 11/4" X 1 1/2"	1
	2	21585	PIPE PLUG ZPS - 1/8" NPT	2
	3	22588	LOCK NUT S.S 3/8"-24	1
	4	27662	IMPELLER B - Ø5.47	1
	5	21865	KEY S.S WOODRUFF #2	1
*	6	27665	GASKET - NI-2085	1
	7	28593	ADAPTOR D - S-60	1
*	8	22272	SEAL ASSEMBLY T-2100 - VITON	1
	9	22131	DRIVE SLEEVE	1
	10	24965	HEX HD. CAPSCREW S.S 5/16-18 X 3/4 PATCH	4
	11	23002	CLAMP ASSY. S.S 5/8 & 3/4	1
	12	21251	HEX HD SCREW S.S 5/16"-18 X .88"	4
	13	21266	LOCKWASHER S.S 3/8"	4

*- RECOMMENDED REPLACEMENT PARTS

