


UPGRADE FOR NEW & EXISTING LIQUID RING COMPRESSORS

GARO® Enhanced Bearing Barrier Kit

Give your compressors a new life with the exclusive GARO Enhanced Bearing Barrier Kit, designed to prevent the ingress of contaminant and the egress of lubrication.

Many benefits in one tool!

- Prevents oil leakage
- Prevents dust from being introduced to the system
- Enhances oil sealing system thanks to the extraordinay oil splash effect
- Increases unit reliability and product life expectancy
- Reduces necessity of inspections
- Increases MTBM





Via Pompei, 15 20052 Monza MB Italy +39 039 839601

www.GDGaro.com

©2018 Garo GDG-ENHANCEDBB-1160 1st Ed. 02/18



Please recycle after use.