


COMPRESSED AIR SYSTEM | 21/2" TO 10"

Big-Lock Tubing



High Quality

Aluminum Piping Systems

Simply stated there is no equal. Big-Lock from Gardner Denver has taken large diameter piping systems to a new level.

Ten times lighter than steel, without compromising any structural strength, the system is easier to install than plastic and delivers a quality of air, gas or vacuum that is equal to that of high cost welded stainless steel systems.

The secret of the Big-Lock system is twofold. First is the tubing design. Big-Lock is manufactured from marine-grade aluminium that affords it the highest level of protection against contamination. This ensures that the media travelling through a system encounters very little turbulence, while enabling high flow rates with minimal pressure losses compared to conventional steel systems.

Secondly, Big-Lock incorporates the world's most highly accepted grooved fitting design. All mechanical contractors will understand the technology and will be able to install a Big-Lock system. We ensure that all fittings coming into contact with the media flowing through a system are manufactured from high quality aluminum so that system integrity will never be compromised. Zero contamination is a priority; it is the only solution to achieve the lowest cost of ownership when operating a piping system.

Big-Lock provides a simple solution for large air/gas/ nitrogen/vacuum users and is, without a doubt, the easiest and fastest system to install. It has the lowest cost of ownership and the best quality of media delivery available.

Outstanding performance from an outstanding product is what we demand and what you should expect from our system.



Simply stated:

There is no equal.



BIG-LOCK COMPLETE

Now switch to Quick-Lock to provide the total solution

Once you have installed a Big-Lock header, it is common to have smaller diameter piping for drops and solid line hook ups to machines and equipment.

Quick-Lock, like Big-Lock, promotes a total metal solution with bore sizes from 20 mm ($\frac{1}{2}$ ") up to 63 mm ($\frac{2}{2}$ ").

The piping is manufactured in the same marine-grade aluminum as Big-Lock but promotes a different range and style of fittings.

Quick-Lock fittings are made from solid brass and nickel-plated to provide a strong and non-corrosive solution. The fitting design is a simple "push to connect" system and requires minimal skill, effort or tooling to install.

It could not be easier

Simply drill a hole in the Big-Lock piping and fix an outlet saddle clamp around the tubing to leave a female threaded connection that allows for the simple conversion between Big-Lock and Quick-Lock.




Attach saddle clamp to Big-Lock pipe with female threaded connection



Screw male thread connector into female connector



Attach Quick-Lock piping to fitting



SMOOTH BORE

HIGH-PERFORMANCE

Don't Jeopardize Air Handling Efficiency

Compressed air piping is responsible for the delivery of compressed air to the point of use. Its material, age and condition impact both system reliability and air quality. Compressed air piping made from iron will rust and corrode, creating buildup on the interior and reducing the functional diameter. This buildup results in pressure drop within the system, contributing to high levels of contamination and poor air quality.



production downtime and dramatically

Smooth internal diameter of tube maintained

■ Ensures lowest cost of ownership of any piping

reduces maintenance costs

throughout life of system

system available

GROOVE

BOLT/NUT

Marine-grade aluminium construction prevents rust and system deterioration


Eliminates scale/corrosion from entering production equipment

Zero corrosion eliminates expensive

Components







Specifications

BIG-LOCK TECHNICAL SPECIFICATIONS

SPECIFICATION	MEASUREMENT				
Max Working Pressure	220 PSI (15 BAR)				
Max Working Temperature	-4°F to 176°F (100% Duty)				
Tubing Material	Aluminum, ASTM 6061-T4 (Marine Grade)				
Tubing Weight	70 mm	0.86 lbs./ft			
	90 mm	1.04 lbs./ft			
	115 mm	1.15 lbs./ft			
	168 mm	3.12 lbs./ft			
	220 mm	4.95 lbs./ft			
Standard Seals	(-4°F to 176°F) Nitrile Rubber				
High Temperature Seals	(-4°F to 300°F) Fluoroelastomer				
Fittings	Aluminum, B-26, 356-T6				
Couplings	Ductile Iron, Galvanized, Grade 65-45-12				
Standards & Approvals	ASME B31.1 Power Piping ASTM F-1476 BOCA CSA B-242 SBCCI				



BIG-LOCK SYSTEM FLOW RATES

PSI	CU FT/MIN						
	70 MM	90 MM	115 MM	168 MM	220 MM		
100	948	1955	3844	10078	20944		
125	1064	2162	4205	11194	23169		
150	1169	2364	4591	12153	25279		
220	1417	2937	5568	14740	30418		

Above flow rates are based on straight line flow allowing for a 1 psi pressure drop per 100 ft over pipe and couplings. For loop systems, flow rates are doubled, i.e. 90 mm tubing at 100 psi flows 3910 cfm

Lifetime Warranty

Gardner Denver is proud to provide our Lifetime Warranty Program covering all pipe and fittings for the Quick-Lock and Big-Lock compressed air product lines. This warranty is possible due to the long history of producing high quality products, continuing our tradition of excellence and customer satisfaction.

We are 100% committed to supplying the finest products available to our customers and always doing our best to exceed their expectations. This Lifetime Warranty is a testament to that commitment!



The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-440-6241 www.gardnerdenver.com/gdproducts







©2019 Gardner Denver, Inc. Printed in U.S.A. GA-BLT 3rd Ed. 4/19

