

CHEMSTEEL SERIES

S205 NON-METALLIC

CHEMSTEEL®

CHEMSTEEL SERIES S205 NON- METALLIC



A full range of accessories are available including: kits for base mounting, or close-coupling, line mount relief valves.

GENERAL DESCRIPTION

Chemsteel pumps are designed to handle common and highly corrosive liquids that must be pumped under pressure. Manufactured to extremely precise tolerance, the Chemsteel pump line prevents system contamination while maintaining the purity and integrity of the liquid being pumped. Its rugged, three-section construction provides ease of servicing and parts replacement.

Helical gearing offers noise reduction by as much as 10db, while the tandem pumps double the output flow for a single fluid, or with isolation, handle other fluids in direct ratio to the first.


Additionally, Chemsteel pumps offer bi-directional operation for applications requiring reversing flow.

LIFE CYCLE/COST OF OWNERSHIP

Pump design and materials selection, together provide the longest life available from a gear pump. *Key attributes include*:

- Gear & bearing combinations of metallic and nonmetallic wear surfaces.
- Slotted bearings to lubricate shaft and gear surfaces.
- Hydraulic porting to balance axial thrust and to reduce wear.
- Ample port sizing to reduce the likelihood of cavitation when inlet pressure is marginal.
- Effective housing seals with elastic memory prevent leakage of corrosives.

PERFORMANCE



Notes: For continuous service: Plastic / Plastic gear combinations are limited to 50 psi. Metal / Plastic gear combinations are limited to 100 psi. Horsepower requirements increase for viscous fluids.

SPECIFIC SOLUTIONS

Gear/bearing design allows for "trimming" for optimizing the pump's maximum flow to reach minimum turndown or to match flow to a specific OEM's requirement. Special materials combinations are available for specific liquids:

- Reinforced Ryton® housing construction.
- Gears available in metallic 316 stainless steel and Alloy C. Also in Teflon®, Ryton® and PEEK®.
- Shafts are 316 stainless steel or Alloy C.
- Bearings available in carbon or Teflon®.

Full range of seal options including lip seal, packing and mechanical designs.

FIT

Connections are female NPT or BSPT, pump hardware is metric and close couple adapters mount to both NEMA and IEC standard motor frame sizes for world wide acceptance.

MAINTENANCE


A three-part housing provides easy disassembly and service. Full size bearings match the gear diameter, and eliminate the need for separate wear plates. TFE encapsulating silicone pump housing seals provide elastic memory to assure an effective long lasting seal and thus avoiding the re-torquing required of pumps using pure TFE. The upper shaft configuration lends itself to in-line pump seal maintenance without the leakage of trapped chemicals from an incompletely drained pump.

To order a **CHEM**kit, simply add a "K" to the end of the model number. A repair kit contains the following parts: seals, bearings, gears, o-rings, shafts, keys, c clips, and retaining ring.

CLOSE-COUPLED DIMENSIONAL



MODEL	S205 NM
maximum flow (gpm) @1750 rpm	3
theoretical displacement (cc/revolution)	7.4
maximum differential pressure (psig)	100
maximum system pressure (psig)	200
maximum speed (RPM)	1800
maximum fluid temperature	200° F
minimum fluid temperature	-40° F
standard port size	1/2 inch FNPT
weight (lbs)	3




adapter code	kit part no.	mo fra	otor ame		D1	2E	2F	н	1 O	1 AP	1 xo	AA	AB	1 AC	AD	AE														
C1	M2AD56R	56C		560		560		560		560		560		560		560		INCHES	3.50	4.88	3.00	ø.34 SLOT	6.88	6.63	2.25	7.14	9.66	18.04	-	9.71
	WIZADJOK			MILLIMETERS	88.9	124	76.2	ø8.6 SLOT	174.8	168.4	57.2	181.4	245.4	458.1	-	246.6														
C2	M2AD45TR	143TC	145TC	INCHES MILLIMETERS	3.50 88.9	5.50 139.7	4.00 5.00 102 127	ø.34 SLOT ø8.6	6.88 174.8	6.63 168.4	2.25 57.2	7.14	9.66	19.23 20.73 488.4 526.5	-	9.53 242.1														
	MZAD451 R	182C	184C	INCHES MILLIMETERS	4.50 114.3	7.50	4.50 5.50 114.3 139.7	ø.41 SLOT ø10.41 SLOT	8.69 220.7	7.88	2.38 60.3	181.4	345.4	21.95 21.17 557.5 537.7	_	10.03 254.8														
C3	M2AD71RE	IEC 71, B14 FACE		INCHES	2.80	4.41	3.54	ø.28 SLOT	5.14	4.69	-	6.64	9.16	18.47	4.00	8.42														
	WIZAD7 TKE			MILLIMETERS	71	112	89.9	ø7 SLOT	130.6	119.1	_	168.7	232.7	469	102	213.9														
C4	M2AD80RE	IEC 80, B14 FACE		IEC 80, B14 FACE				INCHES	3.15	4.92	3.94	ø.39 SLOT	6.00	5.69	-	6.64	9.16	18.70	4.51	8.62										
	WIZADOURE					MILLIMETERS	80	125	100.1	ø10 SLOT	152.4	144.5	-	168.7	232.7	474.9	116	218.9												

1. These dimensions vary depending on hp, enclosure, speed and motor manufacturer. Specifications are subject to change without notification.

PEDESTAL MOUNT DIMENSIONS

	Α	В	С		C		C		С		С		С		С		С		c		С		С		C		C		C		С		C		C		С		D	E	F	G	Н	J	K		L	М	N	0	Р	R	S		Т	
			Mechanical	Pack 1	Lip						Diameter	Standard drive	Lower drive							Mechanical	Lip	Mechanical	Lip																																	
inches	0.50	0.50	1.21"	0.72	2.25	6.67	4.38	3.82	1.12	2.38	0.26	2.38	1.08	2.50	3.41	0.22	2.88	3.50	1.73	2.19	1.73	2.75"	1.73																																	
millimeters		12.7	30.7	18.3	57.2	169.4	111.3	97.0	28.4	60.5	6.6	60.5	27.4	63.5	86.6	5.6	73.2	88.9	43.9	55.6	43.9	69.9	43.9																																	

1. Dimension is approximated with packing nut installed.



ered trademark of DuPont, an equ ent fluoro Ryton® is a registered trademark of Chevron Phillips Chemical, an equivalent polyphen PEEK® is a trademark of Victrex, an equivalent polyetheretherketone may be used. Kalrez® is a trademark of DuPont Dow Elastomers, an equivalent perfluoroelastometer may be u Grafoil® is a trademark of UCAR Carbon Technology, an equivalent may be used.

CH-SP205 R

03/08

ers, an equi