COMPRESSOR DATA SHEET



In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors Rotary Compressor: Fixed Speed

MODEL DATA - FOR COMPRESSED AIR							
1	Manufacturer: Gardner Denver						
	Model Number: STG2-200HP-150psi	Date:	7/21/2020				
2	Air-cooled X Water-cooled	Type:	Screw				
		# of Stages:	1				
3*	Rated Capacity at Full Load Operating Pressure a, e	861.0	acfm ^{a,e}				
4*	Full Load Operating Pressure b	150	psig				
5	Maximum Full Flow Operating Pressure c	150	psig ^c				
6	Drive Motor Nominal Rating	200	hp				
7	Drive Motor Nominal Efficiency	96.2	percent				
8	Fan Motor Nominal Rating (if applicable)	NA	hp				
9	Fan Motor Nominal Efficiency	NA	percent				
10*	Total Package Input Power at Zero Flow ^e	39.2	kW ^e				
11	Total Package Input Power at Rated Capacity and Full Load Operating Pressure ^d	177.60	kW^d				
12*	Package Specific Power at Rated Capacity and Full Load Operating Pressure ^e	20.61	kW/100 cfm ^e				
13	Isentropic Efficiency	80.19	Percent				

^{*}For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator.

Consult CAGI website for a list of participants in the third party verification program:

www.cagi.org

NOTES:

- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex C; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 3) and Electrical Consumption (Item 11) were measured for this data sheet.
- c. Maximum pressure attainable at full flow, usually the unload pressure setting for load/no load control or the maximum pressure attainable before capacity control begins. May require additional power.
- d. Total package input power at other than reported operating points will vary with control strategy.
- e. Tolerance is specified in ISO 1217, Annex C, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
m ³ / min	ft ³ / min	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	+/- 10%
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

Member

ROT 030.1

12/19 Rev ? This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.