



VALUE PLUS | 3-5 HP RECIPROCATING COMPRESSORS

Pump Model VP10

The Solution to Your Application

The Value Plus compressor line was engineered for industrial applications that require an electric driven compressor. Each compressor was designed with top quality bearings, cast iron cylinders and vibration-free compressor pumps to ensure longevity of the compressor package. The Value Plus is another quality product in the Gardner Denver line of air compressors.

Standard Features

- Magnetic starters
- Automatic start/stop operation
- OSHA approved belt guard
- NEMA rated electric motors
- ASME coded air receivers
- Manual tank drain
- 0-300 PSIG air pressure gauge on receiver
- Preset pressure switch
- Available voltages - 208/230/460
- 1-Year package warranty
- 1-Year pump warranty

Available Options

- Vibration isolators

Gardner
Denver

BARE PUMP

MODEL	APPROX. SHIP WEIGHT (LBS)	BORE INCHES	STROKE INCHES	STAGE #	# OF CYLINDERS	DIAM. FLYWHEEL INCHES	DIAM. PULLEY INCHES	OIL CAPACITY QTS.	MAX PUMP RPM
VP10	39	2.5 × 2.5	1.9	1	2	10	3.95	5	860

SIMPLEX TANK MOUNTED UNITS

MOTOR HP	TANK CAPACITY GAL.	VALUE PLUS CDSVPA	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	VOLTAGE	PHASE	CFM DELIVERY @ 100 PSI	TANK OUTLET
3	60	3V60E	30 × 20 × 65.5	330	230	1	10.2	.5" NPT

Gardner Denver®

Gardner Denver, Inc.

1800 Gardner Expressway
Quincy, IL 62305
866-440-6241

www.gardnerdenver.com/gdproducts



©2018 Gardner Denver, Inc. Printed in U.S.A.
GRCS-VP-VP10 1st Ed. 2/18

Please recycle after use.