## **COMPRESSOR DATA SHEET**



## Federal Uniform Test Method for Certain Air Compressors Not Applicable

## **Rotary Compressor: Variable Frequency Drive**

1 Manu	facturer: Gard	ner Denver			
Mode	Model Number: VST225-150hp(2S)-125psi			Date:	01/04/21
2	Air-cooled X	Water-cooled		Type:	Screw
X	Lubricated	Oil Free	#	of Stages:	2
s* Full L	oad Operating Pressu	re <sup>b</sup>	125	psig <sup>b</sup>	
4 Drive	Drive Motor Nominal Rating		2 x 150	hp	
5 Drive	Drive Motor Nominal Efficiency		94.0	percen	
5 Fan M	Fan Motor Nominal Rating (if applicable)		NA	hp	
7 Fan M	Iotor Nominal Efficie	ncy	NA	percent	
Ir	Input Power (kW)		Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>	
	271.35		1607.0	16.89	
	232.05		1366.0	16.99	
;*	193.99		1124.9	17.25	
	155.80		883.9	17.63	
	116.90		642.8	18.19	
	73.30		377.0	19.44	
* Total	Package Input Power	at Zero Flow <sup>c, d</sup>	0.0	kW	
0	35.00 30.00 30.00 30.00 25.00 15.00 10.00 0.0	200.0 400.0 600.0	) 800.0 1000.0 1200.	0 1400.0 160	-

Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35 X-Axis Scale, 0 to 25% over maximum capacity

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator

Consult CAGI website for a list of participants in the third party verification program:

CAGI Compressed Air & Gas Institute

Member

a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.

b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.

- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:

NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

		me Flow Rate	Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power	
	$\underline{m^3 / \min}$	<u>ft<sup>3</sup> / min</u>	%	%	%	
	Below 0.5	Below 17.6	+/- 7	+/- 8		
	0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%	
	1.5 to 15	53 to 529.7	+/- 5	+/- 6		
ROT 031.2	Above 15	Above 529.7	+/- 4	+/- 5		

12/19 R3 This form was developed by the Compressed Air and Gas Institute for the use of its members participating in the PVP. CAGI has not independently verified the reported data.

Configurator: VST225-260B

www.cagi.org