

5 & 7.5 HP | RECIPROCATING AIR COMPRESSORS







## Ultimate Value Exceptional Performance

## A Winning Combination

Gardner Denver compressors are proven units, known for their reliability over decades of use. We know our products and understand how they operate in many different operating environments. No matter the application, Gardner Denver gets the job done.

# Value & Quality Collide

The VP-Series compressors are engineered to deliver both value and quality in one simple package. Each compressor is designed with top quality bearings, cast iron cylinders, vibration free compressor pumps to insure longevity of the compressor package.

## Reliable, Economical, Easily Installed

Simple & Strong, the VP-Series air compressors are ideal for light industrial, commercial and professional applications.





## The Design Advantage


### **VP-Series**

- 5-7.5 HP Range
- 125-150 PSIG
- 11.4-22.7 CFM
- Vertical Air Receivers

### **Compressor Pump Specifications**

- Splash Lubricated
- Single- & Two-Stage Design
- 100% Cast Iron
- Oil Level Sight Glass (VP-55 and VP-100)
- Pressure Relief Valves
- Large Flywheel Blades for Maximum Cooling
- Reed Valve Design (VP-40 and VP-55)
- Disc Valve Design (VP-100)

- Deep Finned Intercooler
- Industrial Grade Intake Filter and Silencer
- Factory Filled with Lubricant
- All Pumps are Factory Tested Prior to Shipment



# It's all in the Details

### Standard Equipment

- Magnetic Starters\*
- Automatic Start/Stop Operation
- OSHA Approved Belt Guard
- NEMA Rated Electric Motors
- ASME Coded Air Receivers
- Manual Tank Drain
- Air Pressure Gauge
- Preset Pressure Switch

\*Option not available with 3600 RPM motors



# Design Dependable Reciprocating Confidence VP-Series Durability Package Benefit Convenience Performance Service Longevity

### Pump Model VP-40 VP-SERIES | 5 HP RECIPROCATING Compressors

	MOTOR HP	TANK	VERTICAL PACKAGES						PUMP DETAIL		125 PSI RATING	
		CAPACITY GAL.	VP-SERIES MODEL	VOLTAGE	PART NUMBER	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	CYLIN- DERS	STAGES	RPM	CFM DEL'Y	
-	5*	60	VP5-40-6	230/1/60	317CDS8016	35 x 20 x 66	350	3	1	1220	11.4	

\*3600 RPM motor

Pump Model VP-55

### VP-SERIES | 5 HP RECIPROCATING Compressors

M	MOTOR HP	TANK CAPACITY GAL.	VERTICAL PACKAGES					PUMP DETAIL		150 PSI RATING	
			VP-SERIES MODEL	VOLTAGE	PART NUMBER	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	CYLIN- DERS	STAGES	RPM	CFM DEL'Y
	5	80	VP5-55-8	230/1/60	318CDS8016	35 x 25 x 69	530	3	2	940	15.2

### Pump Model VP-100

VP-SERIES | 7.5 HP RECIPROCATING Compressors

MOTOR	TANK CAPACITY GAL.	VERTICAL PACKAGES					PUMP DETAIL		125 PSI RATING	
MOTOR HP		VP-SERIES MODEL	VOLTAGE	PART NUMBER	DIMENSIONS L × W × H INCHES	APPROX. SHIP WEIGHT LBS.	CYLIN- DERS	STAGES	RPM	CFM DEL'Y
7.5	80	VP7-100-8	230/1/60 230/3/60 460/3/60	319CDS8016 320CDS8016 321CDS8016	40 x 25 x 71	720	4	2	570	22.7

## Sales & Service Distributors Across America

## An Extensive Network

By leveraging the extensive network of Gardner Denver factory-trained authorized local distributors, your sales, service and technical support needs can be handled quickly and easily.



# The leader in every market we serve by continuously improving all business processes with a focus on innovation and velocity



#### Gardner Denver, Inc.

1800 Gardner Expressway Quincy, IL 62305 866-440-6241 www.gardnerdenver.com/gdproducts

©2019 Gardner Denver, Inc. Printed in U.S.A. GR-VP 1st Ed. 5/19 Supersedes GR-VALUE-PLUS 1st 6/17



Please recycle after use.

