

**COMPRESSOR DATA SHEET**



**In Accordance with Federal Uniform Test Method for Certain Lubricated Air Compressors**

**Rotary Compressor: Variable Displacement**

MODEL DATA - FOR COMPRESSED AIR			
1	Manufacturer: <b>Gardner Denver</b>		
2	Model Number: <b>SAV-200hp-EAU-100psi</b>		Date: <b>01/04/21</b>
	<input type="checkbox"/> Air-cooled	<input checked="" type="checkbox"/> Water-cooled	Type: <b>Screw</b>
	<input checked="" type="checkbox"/> Lubricated	<input type="checkbox"/> Oil Free	# of Stages: <b>1</b>
3*	Full Load Operating Pressure <sup>b</sup>	<b>100</b>	psig <sup>b</sup>
4	Drive Motor Nominal Rating	<b>200</b>	hp
5	Drive Motor Nominal Efficiency	<b>95.8</b>	percent
6	Fan Motor Nominal Rating (if applicable)	<b>N/A</b>	hp
7	Fan Motor Nominal Efficiency	<b>N/A</b>	percent
8*	Input Power (kW)	Capacity (acfm) <sup>a,d</sup>	Specific Power (kW/100 acfm) <sup>d</sup>
	168.0	<b>934</b>	<b>17.99</b>
	156.3	<b>841</b>	<b>18.59</b>
	134.5	<b>654</b>	<b>20.57</b>
	116.3	<b>467</b>	<b>24.90</b>
	110.9	<b>374</b>	<b>29.65</b>
9*	Total Package Input Power at Zero Flow <sup>c, d</sup>	<b>30.2</b>	kW
10	Isentropic Efficiency at Full Flow Rated Capacity and Full Load Operating Pressure	<b>73.9</b>	%
11	<div style="text-align: center;"> <p><b>Note: Graph is only a visual representation of the data in Section 8</b>                      Note: Y-Axis Scale, 10 to 35, + 5kW/100acfm increments if necessary above 35                      X-Axis Scale, 0 to 25% over maximum capacity</p> </div>		

\*For models that are tested in the CAGI Performance Verification Program, these items are verified by the third party administrator  
 Consult CAGI website for a list of participants in the third party verification program: [www.cagi.org](http://www.cagi.org)



- a. Measured at the discharge terminal point of the compressor package in accordance with ISO 1217, Annex E; ACFM is actual cubic feet per minute at inlet conditions.
- b. The operating pressure at which the Capacity (Item 8) and Electrical Consumption (Item 8) were measured for this data sheet.
- c. No Load Power. In accordance with ISO 1217, Annex E, if measurement of no load power equals less than 1%, manufacturer may state "not significant" or "0" on the test report.
- d. Tolerance is specified in ISO 1217, Annex E, as shown in table below:  
 NOTE: The terms "power" and "energy" are synonymous for purposes of this document.

Member

Volume Flow Rate at specified conditions		Volume Flow Rate	Specific Energy Consumption	No Load / Zero Flow Power
$m^3 / min$	$ft^3 / min$	%	%	%
Below 0.5	Below 17.6	+/- 7	+/- 8	
0.5 to 1.5	17.6 to 53	+/- 6	+/- 7	+/- 10%
1.5 to 15	53 to 529.7	+/- 5	+/- 6	
Above 15	Above 529.7	+/- 4	+/- 5	

ROT 032.1