

## VERTICAL TWO STAGE, CABINET ENCLOSED, ELECTRIC MOTOR DRIVEN - CICVWA

| Unit Model | HP  | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |      |      | 50 PSIG       | 175 PSIG |             |           |                         |        |
| 5EVTR20    | 5   | VTS  | 740  | 21.7          | 15.8     | 4.72 & 2.56 | 1.97      | 40 x 37 x 65¾           | 1053   |
| 7EVTR20    | 7.5 | VTS  | 1065 | 31.6          | 21.2     | 4.72 & 2.56 | 1.97      | 40 x 37 x 65¾           | 1058   |
| 10EVTS35   | 10  | VTS  | 1450 | 43.0          | 35.4     | 4.72 & 3.54 | 1.97      | 40 x 37 x 65¾           | 1096   |
| 15EWTS55   | 15  | WTS  | 1140 | 69.0          | 48.0     | 4.72 & 3.54 | 1.97      | 40 x 37 x 65¾           | 1244   |

## VERTICAL SINGLE STAGE, CABINET ENCLOSED, ELECTRIC MOTOR DRIVEN - CICVWA

| Unit Model | HP  | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |      |      | 50 PSIG       | 100 PSIG |             |           |                         |        |
| 5EVTS35    | 5   | VTS  | 740  | 21.7          | 16.8     | 4.72        | 1.97      | 40 x 37 x 65¾           | 999    |
| 7EVTS35    | 7.5 | VTS  | 1065 | 31.6          | 25.9     | 4.72        | 1.97      | 40 x 37 x 65¾           | 1004   |
| 10EVTS35   | 10  | VTS  | 1450 | 43.0          | 35.2     | 4.72        | 1.97      | 40 x 37 x 65¾           | 1040   |
| 15EWTS55   | 15  | WTS  | 1140 | 69.0          | 56.5     | 4.72        | 2.36      | 40 x 37 x 65¾           | 1180   |

## HORIZONTAL DUPLEX TANK MOUNT, TWO STAGE, ELECTRIC MOTOR DRIVEN - CIDVWA

| Unit Model  | HP      | Tank Size GA | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|-------------|---------|--------------|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|             |         |              |      |      | 125 PSIG      | 175 PSIG |             |           |                         |        |
| 12TD5VTR20  | 5 (2)   | 120          | VTR  | 1000 | 32.2          | 31.6     | 4.72 & 2.56 | 1.97      | 88¼ x 57¼ x 60½         | 2575   |
| 25TD5VTR20  | 5 (2)   | 250          | VTR  | 1000 | 32.2          | 31.6     | 4.72 & 2.56 | 1.97      | 84 x 67 x 72            | 2935   |
| 12TD7VTR20  | 7.5 (2) | 120          | VTR  | 1300 | 42.8          | 42.4     | 4.72 & 2.56 | 1.97      | 88¼ x 57¼ x 60½         | 2750   |
| 25TD7VTR20  | 7.5 (2) | 250          | VTR  | 1300 | 42.8          | 42.4     | 4.72 & 2.56 | 1.97      | 84 x 67 x 72            | 3110   |
| 12TD10WTR45 | 10 (2)  | 120          | WTR  | 1065 | 72.0          | 70.8     | 4.72 & 3.54 | 1.97      | 88¼ x 57¼ x 60½         | 2820   |
| 25TD10WTR45 | 10 (2)  | 250          | WTR  | 1065 | 72.0          | 70.8     | 4.72 & 3.54 | 1.97      | 84 x 67 x 72            | 3220   |
| 12TD15WTR45 | 15 (2)  | 120          | WTR  | 1450 | 96.8          | 96.0     | 4.72 & 3.54 | 1.97      | 88¼ x 57¼ x 60½         | 3060   |
| 25TD15WTR45 | 15 (2)  | 250          | WTR  | 1450 | 96.8          | 96.0     | 4.72 & 3.54 | 1.97      | 84 x 67 x 72            | 3480   |

## HORIZONTAL DUPLEX TANK MOUNT, SINGLE STAGE, ELECTRIC MOTOR DRIVEN - CIDVWA

| Unit Model  | HP      | Tank Size GA | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|-------------|---------|--------------|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|             |         |              |      |      | 50 PSIG       | 100 PSIG |             |           |                         |        |
| 12TD5VTS35  | 5 (2)   | 120          | VTS  | 740  | 43.4          | 33.6     | 4.72        | 1.97      | 88¼ x 57¼ x 60½         | 2545   |
| 25TD5VTS35  | 5 (2)   | 250          | VTS  | 740  | 43.4          | 33.6     | 4.72        | 1.97      | 84 x 67 x 72            | 1875   |
| 12TD7VTS35  | 7.5 (2) | 120          | VTS  | 1065 | 63.2          | 51.8     | 4.72        | 1.97      | 88¼ x 57¼ x 60½         | 2760   |
| 25TD7VTS35  | 7.5 (2) | 250          | VTS  | 1065 | 63.2          | 51.8     | 4.72        | 1.97      | 84 x 67 x 72            | 3125   |
| 12TD10VTS35 | 10 (2)  | 120          | VTS  | 1450 | 86.0          | 70.4     | 4.72        | 1.97      | 88¼ x 57¼ x 60½         | 2815   |
| 25TD10VTS35 | 10 (2)  | 250          | VTS  | 1450 | 86.0          | 70.4     | 4.72        | 1.97      | 84 x 67 x 72            | 3220   |
| 12TD15WTS55 | 15 (2)  | 120          | WTS  | 1140 | 138.0         | 113.0    | 4.72        | 2.36      | 88¼ x 57¼ x 60½         | 3055   |
| 25TD15WTS55 | 15 (2)  | 250          | WTS  | 1140 | 138.0         | 113.0    | 4.72        | 2.36      | 84 x 67 x 72            | 3440   |

**HORIZONTAL BASE MOUNT, TWO STAGE, ELECTRIC MOTOR DRIVEN - CIBVWA**

| Unit Model | HP  | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |      |      | 125 PSIG      | 175 PSIG |             |           |                         |        |
| 5VTR20     | 5   | VTR  | 1000 | 16.1          | 15.8     | 4.72 & 2.56 | 1.97      | 57¼ x 37½ x 37¾         | 1035   |
| 7VTR20     | 7.5 | VTR  | 1300 | 21.4          | 21.2     | 4.72 & 2.56 | 1.97      | 57¼ x 37½ x 37¾         | 1115   |
| 10WTR45    | 10  | WTR  | 1065 | 36.0          | 35.4     | 4.72 & 3.54 | 1.97      | 57¼ x 37½ x 37¾         | 1155   |
| 15WTR45    | 15  | WTR  | 1450 | 48.4          | 48.0     | 4.72 & 3.54 | 1.97      | 57¼ x 37½ x 37¾         | 1195   |

**HORIZONTAL BASE MOUNT, SINGLE STAGE, ELECTRIC MOTOR DRIVEN - CIBVWA**

| Unit Model | HP  | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |      |      | 50 PSIG       | 100 PSIG |             |           |                         |        |
| 5VTS335    | 5   | VTS  | 740  | 21.7          | 16.8     | 4.72        | 1.97      | 57¼ x 37½ x 37¾         | 1030   |
| 7VTS35     | 7.5 | VTS  | 1065 | 31.6          | 25.9     | 4.72        | 1.97      | 57¼ x 37½ x 37¾         | 1105   |
| 10VTS35    | 10  | VTS  | 1450 | 43.0          | 35.2     | 4.72        | 1.97      | 57¼ x 37½ x 37¾         | 1120   |
| 15WTS55    | 15  | WTS  | 1140 | 69.0          | 56.5     | 4.72        | 2.36      | 57¼ x 37½ x 37¾         | 1180   |

**HORIZONTAL TANK MOUNT, TWO STAGE, ELECTRIC MOTOR DRIVEN - CISVWA**

| Unit Model | HP  | Tank Size | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|-----------|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |           |      |      | 125 PSIG      | 175 PSIG |             |           |                         |        |
| 12T5VTR20  | 5   | 120       | VTR  | 1000 | 16.1          | 15.8     | 4.72 & 2.56 | 1.97      | 69 x 37½ x 67           | 1480   |
| 25T5VTR20  | 5   | 250       | VTR  | 1000 | 16.1          | 15.8     | 4.72 & 2.56 | 1.97      | 92 x 37½ 73             | 1845   |
| 12T7VTR20  | 7.5 | 120       | VTR  | 1300 | 21.4          | 21.2     | 4.72 & 2.56 | 1.97      | 69 x 37½ x 67           | 1545   |
| 25T7VTR20  | 7.5 | 250       | VTR  | 1300 | 31.4          | 21.2     | 4.72 & 2.56 | 1.97      | 92 x 37½ 73             | 1910   |
| 12T10WTR45 | 10  | 120       | WTR  | 1065 | 36.0          | 35.4     | 4.72 & 3.54 | 1.97      | 69 x 37½ x 67           | 1570   |
| 25T10WTR45 | 10  | 250       | WTR  | 1065 | 36.0          | 35.4     | 4.72 & 3.54 | 1.97      | 92 x 37½ 73             | 2145   |
| 12T15WTR45 | 15  | 120       | WTR  | 1450 | 48.4          | 48.0     | 4.72 & 3.54 | 1.97      | 69 x 37½ x 67           | 1725   |
| 25T15WTR45 | 15  | 250       | WTR  | 1450 | 48.4          | 48.0     | 4.72 & 3.54 | 1.97      | 92 x 37½ 73             | 2145   |

**HORIZONTAL TANK MOUNT, SINGLE STAGE, ELECTRIC MOTOR DRIVEN - CISVWA**

| Unit Model | HP  | Tank Size | Pump | RPM  | CFM Delivery* |          | Bore DIA IN | Stroke IN | Dimensions L x W x H IN | WT LBS |
|------------|-----|-----------|------|------|---------------|----------|-------------|-----------|-------------------------|--------|
|            |     |           |      |      | 50 PSIG       | 100 PSIG |             |           |                         |        |
| 12T5VTS35  | 5   | 120       | VTS  | 740  | 21.7          | 16.8     | 4.72        | 1.97      | 69 x 37½ x 67           | 1515   |
| 25T5VTS35  | 5   | 250       | VTS  | 740  | 21.7          | 16.8     | 4.72        | 1.97      | 92 x 37½ 73             | 1875   |
| 12T7VTS35  | 7.5 | 120       | VTS  | 1065 | 31.6          | 25.9     | 4.72        | 1.97      | 69 x 37½ x 67           | 1530   |
| 25T7VTS35  | 7.5 | 250       | VTS  | 1065 | 31.6          | 25.9     | 4.72        | 1.97      | 92 x 37½ 73             | 1890   |
| 12T10VTS35 | 10  | 120       | VTS  | 1450 | 43.0          | 35.2     | 4.72        | 1.97      | 69 x 37½ x 67           | 1550   |
| 25T10VTS35 | 10  | 250       | VTS  | 1450 | 43.0          | 35.2     | 4.72        | 1.97      | 92 x 37½ 73             | 1910   |
| 12T15VTS55 | 15  | 120       | WTS  | 1140 | 69.0          | 56.5     | 4.72        | 2.36      | 69 x 37½ x 67           | 1720   |
| 25T15VTS55 | 15  | 250       | WTS  | 1140 | 69.0          | 56.5     | 4.72        | 2.36      | 92 x 37½ 73             | 2125   |