

Bronze Pedestal Rotary Gear Pumps Model N7000 Series

Model N7000 3/4" NPT Ports



Model N7000R



FEATURES:

- Bronze Corrosion Resistant Castings
- Special Cast Bronze Gears
- Stainless Steel Shafts & Fasteners
- Formed Ring Seal Packing (Lip & Mechanical Seals are available)
- Heavy Duty Carbon Bearings (Self Lubricating)
- Positive Displacement Flow

DRIVE:

Either direct drive with flexible coupling or pulley drive can be used. Make sure both flexible coupling halves are properly aligned. When using a pulley, do not overtighten the belt. Also, to absorb belt side thrust at higher pressures and larger size pumps, an external ball bearing support is recommended -- consult factory.


LIQUIDS AND TEMPERATURE:

Service life will be increased substantially if the liquid pumped is clean and has some degree of lubricity. These positive displacement pumps have tight tolerances. Fine abrasives like sand, silt, or powders in suspension will accelerate pump wear and reduce throughput.

Liquids compatible with bronze and stainless steel can be pumped providing proper seal has been specified. (See chemical compatibility or check factory.) When possible, flush the pump after each usage.

PERFORMANCE:

Water capacity 70° F



* For pressures over 100 p.s.i., the above selections are suitable for pumping fluids with lubricity (eq. oils, polymers). Service life will decrease for fluids without lubricity (eq. water, solvents).

Temperature extremes are detrimental to service life and should be avoided. Basic metals of construction allow a temperature range of -40 to 400° F. Some lip and mechanical seal elastomers have a limit of 212° F (see engineering data or check factory). Allowing a liquid to freeze in the pump can cause damage

SUCTION LIFT:


Close tolerances and the positive pumping action make the rotary gear pump capable of lifting water on the suction side as high as 20 feet. Though gear pumps are self priming, a foot valve is recommended. If possible, wet the gears with liquid to be pumped for the first dry start. Liquid retained in the system and gear chambers serves to "wet" the pump on subsequent starts.

BY-PASS AND ROTATION:

The pump by-pass is not intended to be a metering or flow control device. Its main purpose is to function as a pressure relief when the desired set point is exceeded, overheating can occur within 5-10 minutes if the discharge line is completely shut off for extended periods.


Reversing rotation reverses the "IN" and "OUT" ports and the location of the by-pass ports have to be reversed.

The by-pass valve is factory set at 50 psi. To increase the set-point, turn the by-pass valve adjusting screw in a clockwise direction.



Bronze Pedestal Rotary Gear Pumps

Model N7000 Series



		1	2		3	4	5	6	7	8	9	10
		Packnut or Retaining Ring	Packing	Seal	Body	Bearing	Drive Gear Assy	Idle Gear Assy	O-ring	Cover	Screw	Ball
Model	Seal Arrangement	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 4	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 8	Qty. 1
N7000	Packing	1762	5479	NA	9324NE1N	5091	33015	32959	9797-045	9326NN5N	5385	NA
N7000S3	NBR Lip	NA	NA	5463	9324NE2N	5091	33015	32959	9797-045	9326NN5N	5385	NA
N7000S15	FKM Lip	NA	NA	9997	9324NE2N	5091	33015	32959	9797-045	9326NN5N	5385	NA
N7000S16	NBR Bellows Mech.	5374	NA	32202	9374NE9N	5091	33043	32959	9797-045	9326NN5N	5385	NA
N7000S17	FKM Bellows Mech.	5374	NA	32235	9374NE9N	5091	33043	32959	9797-045	9326NN5N	5385	NA
N7000S18	PTFE Wedge Mech.	5374	NA	32923	9374NE6N	5091	33043	32959	9355-045	9326NN5N	5385	NA
Relief Valve Versions: N7000R, N7000RS3, N7000RS15, N7000RS16, N7000RS17, N7000RS18												6217

	11	12	13	14	15	16	17	18	19	20	21	22	23	
	Plug Nut	Spring	Adj. Screw	Locknut	Bypass Nut	O-Ring Locknut	O-Ring Plug Nut	Dowel Pin	Retaining Ring	Pipe Plug	Tag	Tag Screw	Lock Ring	Repair Kit*
Model	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 1	Qty. 2	Qty. 1	Qty. 2	Qty. 1	Qty. 1	Qty. 1	Qty. 2	Qty. 1	
N7000	NA	NA	NA	NA	NA	NA	NA	8885	NA	NA	9344	9345	NA	10638
N7000S3	NA	NA	NA	NA	NA	NA	NA	8885	NA	NA	9344	9345	NA	11258
N7000S15	NA	NA	NA	NA	NA	NA	NA	8885	NA	NA	9344	9345	3033	12107
N7000S16	NA	NA	NA	NA	NA	NA	NA	8885	5382	NA	9344	9345	NA	12128
N7000S17	NA	NA	NA	NA	NA	NA	NA	8885	5382	NA	9344	9345	NA	12129
N7000S18	NA	NA	NA	NA	NA	NA	NA	8885	5382	6052	9344	9345	NA	12130
Relief Valve Versions	5278R	5277	5275	1642D	5276	9797-022	9797-019							

^{*} All Repair Kits contain items 2, 4, 5, 6, 7

 $NBR = A crylonitrile - Butadiene \\ PTFE = Polytetra fluorethylene \\ FKM = Fluoroelas tomer \\$



OBERDORFER PUMPS

by Gardner Denver

5900 Firestone Drive, Syracuse, NY 13206 Phone: (800) 448-1668; (315) 437-0361 • Fax: (315) 463-9561 Visit **www.oberdorfer-pumps.com** to find in-depth descriptions of the world's leading high-quality, dependable pumps.

Due to ongoing product improvements, data shown here is subject to change without notice. Contact Oberdorfer Pumps for latest specifications.